

DESCRIPTION

- Metal construction with chrome plated, antique nickel, LifeShine® brushed nickel, oil-rubbed bronze or wrought iron finishes
- 1/2" IPS connections
- Includes metal pop-up waste assembly
- Includes hot and cold temperature indicator
- Includes optional 3 hole deck plate (escutcheon)

OPERATION

- Pivot action lever style handle
- Temperature controlled by 180° arc of handle travel

FLOW

- Aerator is limited to 2.2 gpm max (8.3 L/min)

CARTRIDGE


- 1225 cartridge design
- Nonmetallic and stainless steel material

STANDARDS

- Third party certified to CSA B125, ASME A112.18.1M, ANSI A117.1, and all applicable requirements referenced therein
- Certified to ANSI/NSF 61/9
- Complies with California Proposition 65 and with the Federal Safe Drinking Water Act

WARRANTY

- Lifetime limited warranty against leaks, drips and finish defects to the original consumer purchaser
- 5 year warranty if used in commercial installations




KINGSLEY™ Single-Handle Lavatory Faucet

Models: 6102, 6102AN, 6102BN,
6102ORB, 6102WR

NOTE: THIS FAUCET IS DESIGNED TO BE
INSTALLED THRU 1 HOLE, 1-1/8" MIN. DIA.

***Use A1616 Extension Kit for
Vessel Sink Applications**



CRITICAL DIMENSIONS

(DO NOT SCALE)