






CLR2160

2000 SERIES

FEATURES

PERFORMANCE

- Daily ice rate of up to 60 lbs and storage of up to 30 lbs of restaurant quality clear ice $(7/8" W \times 7/8" H \times 7/8" L)$
- Drain required and drain line kit is included to ensure proper installation
- Touch glass digital control featuring easy view command center manages key functions such as adjusting desired cube density with a single touch
- Easiest clear ice machine to clean and the clean indicator alert lets you know when it's time to clean the unit, the 45 minute cleaning cycle ensures high quality ice production and helps maintain proper operation
- Silence mode temporarily suspends ice making for three hours
- Sabbath / Blackout mode turns off all lighting, controls display and automatically resets after 36 hours
- No defrosting required
- UL residential and commercial listings



- Lighted white interior optimizes easy viewing of high quality clear ice cubes
- Heavy duty ice scoop is included and may be positioned according to user preference
- Standard commercial stainless steel handle is interchangeable with professional handle option for stainless steel model
- Self-closing door ensures a positive door seal and prevents door bounce back
- Full wrap stainless door on stainless model and unit must be ordered right or left
- Black, white and overlay model door is field reversible
- Black vinyl clad textured cabinet is more resistant to scratching, peeling and flaking
- Unit can be built-in or freestanding providing a custom aesthetic
- Black and white models will accept a 1/4" insert panel to match with surrounding decor
- Optional full 3/4" overlay panel on black and white models requires purchase of overlay kit PN: U-OL 2115
- Allow a 2-1/2" clearance on hinged side for 90° door opening when installed adjacent to a wall (for stainless steel model)
- Allow I/4" width overall for proper installation (see backside for details)
- No additional clearance around sides, top or rear of unit is needed for ventilation
- Durable, factory installed level legs provide a more precise undercounter fit
- Do not obstruct front grille air flow



Overlay


White


Customize clear ice cube density with a single touch for varying user preferences



Produces 32 clear ice cubes per cycle (7/8" W x $7/8" H \times 7/8" L$

INTERIOR / EXTERIOR





CLR2160 Stainless, Black, White and Overlay Models * Add 3/4" to depth for drain line clearance

DIMENSIONS AND SPECIFICATIONS

OVERALL DIMENSIONS

34-1/8" (86.6) Height Width 15" (38.1) 23-3/16" (58.9) Depth

Shipping weight:

100 lbs (45kg) 100 lbs (45kg) Black and white models Stainless model

4.0 Running amps 26.5 Maximum start-up amps

110/115 volt, 60 Amps pertain to voltage rating

Approximate daily ice production Up to 60 lbs Ice storage Up to 30 lbs

CLR2160	
Stainless Right hand, no pump	U-CLR2160S-00
Stainless Right-hand, with pump	U-CLR2160S-40
Stainless Left-hand, no pump	U-CLR2160S-01
Stainless Left-hand, with pump	U-CLR2160S-40
Black, no pump	U-CLR2160B-00
Black, with pump	U-CLR2160B-40
White, no pump	U-CLR2160W-00
White, with pump	U-CLR2160W-40
Overlay	U-CLR2160B-00 with Overlay kit U-OL2115B

Please visit www.u-line.com for installation guide.

All specifications are subject to change without notice.

