Buy it for looks. Buy it for life.®

Specifications

FAUCET DESCRIPTION

Metal construction with various finishes identified by suffix
Includes showerhead, arm, flange and diverter spout

OPERATION

- · Lever style handle with temperature indicator on the escutcheon
- Handle operates counterclockwise through a 270° arc with off at 6 o'clock and maximum hot at the 9 o'clock position. Shut off in clockwise direction
- Adjustable temperature limit stop to control maximum hot water temperature
- Pressure balancing mechanism maintains selected discharge temperature to \pm 3.6° F ($\pm 2^\circ$ C)

FLOW

- Showerhead is limited to 2.5 gpm (9.5 L/min) at 80 psi
- EP suffix models are limited to 1.75 gpm (6.6 L/min) at 80 psi
- NH suffix models contain no showerhead

CARTRIDGE


- 1222 cartridge design
- Nonmetallic/nonferrous and stainless steel materials
- Accommodates back to back installations

STANDARDS

- Third party certified to meet ASME A112.18.1/CSA B125.1 and all applicable requirements referenced therein
- EP suffix models are IAPMO Green listed and third party certified to WaterSense[®]
- ADA 🛃 for lever handle

WARRANTY


- · Lifetime limited warranty against leaks, drips and finish defects
- to the original consumer purchaser
- 5 year warranty if used in commercial installations




90 DEGREE [™] POSI-TEMP[°] Single-Handle Tub/Shower Trim Kit

Model: TS2711 series - valve trim only TS2712 series - shower trim only TS2713 series - tub/shower trim only

Valves: 62300, 2500 series





CRITICAL DIMENSIONS

(DO NOT SCALE)