





Stainless





Black

Overlay

# CLRCO2175

#### 6444#W vm w

### **FEATURES**

**PERFORMANCE** 

INTERIOR / EXTERIOR

- 2.5 cubic feet overall refrigerator capacity maximizes storage
- Daily ice rate of up to 40 lbs and storage of up to 15 lbs of clear ice cubes  $(1/2"W \times 3/4"H \times 2-1/2"L)$
- Unit can be ordered unit with our without factory installed P60 drain pump
- Drain required, drain line kit included to ensure proper installation
- Touch glass digital control featuring easy view command center manages key functions and provides user alerts such as an audible door open alarm
- Digital controlled passive cooling system provides a stable and consistent environment for optimum food and beverage storage
- Temperature setting from 34 to 45° F provides flexibility for preserving a wide variety of items
- Sabbath / Blackout mode turns off all lighting, controls display and automatically resets after 36 hours
- Patented frost-free technology
- UL residential listing
- Lighted white interior allows for easy viewing of contents
- Three tempered glass shelves with bullnose edge to maximize storage potential
- Two in-door storage bins provide easy access and storage flexibility
- Standard commercial stainless steel handle is interchangeable with professional handle option on stainless steel model
- Full wrap stainless door on stainless model must be ordered right or left hand hinged
- Black and overlay door is field reversible
- · Black vinyl clad textured cabinet is more resistant to scratching, peeling and flaking




The Combo® Models bring together abundant ice supply with generous refrigeration capacity in the convenience of one unit.




Single Zone Passive Cooling System featured in CLRCO2175.

- Unit can be built-in or freestanding providing a custom aesthetic
- Black model will accept a 1/4" insert panel
- Optional full 3/4" overlay panel on black and white models requires purchase of overlay kit PN: U-OL2175 and can be fully integrated into all styles of cabinetry
- Allow a 2-1/2" clearance on hinged side for 90° door opening when installed adjacent to a wall (for stainless steel model)
- Allow I/4" width overall for proper installation (see backside for details)
- No additional clearance around sides, top or rear of unit is needed for ventilation
- Durable, factory installed level legs provide a more precise undercounter fit
- Do not obstruct front grille air flow

INTEGRATION





## CLRCO2175S Stainless Model and CLRCO2175B Black Model

\* Add 3/4" to depth for water line clearance

### **DIMENSIONS AND SPECIFICATIONS**

#### **OVERALL DIMENSIONS**

Height Width	34-1/8" (86.6) 23-15/16" (60.8)
Depth	23" (58.4)
With stainless steel handle	24-7/8" (63.2)

### Shipping weight:

Black model 143 lbs (65 kg) Stainless model 137 lbs (62 kg)

4.0 Running amps 26.5 Maximum start-up amps

Amps pertain to voltage rating 110/115 volt, 60 Hz

# Capacities:

Defrost technology Automatic defrost Refrigerator volume 2.5 Cu. Ft Freezer volume N/A

Approximate daily ice production Up to 40 lbs Up to 15 lbs Ice storage

CLRC02175	
Stainless Right-hand, no pump	U-CLRCO2175S-00
Stainless Right-hand, with pump	U-CLRCO2175S-40
Stainless Left-hand, no pump	U-CLRCO2175S-01
Stainless Left-hand, with pump	U-CLRCO2175S-41
Black, no pump	U-CLRCO2175B-00
Black, with pump	U-CLRCO2175B-40
Overlay	U-CLRCO2175B with Overlay kit U-OL2175B

Please visit www.u-line.com for installation guide.

All specifications are subject to change without notice.

