# Little GIANT®

# SPEEDI DUCT™ AND HVAC INSTALLATION ACCESSORIES





# SPEEDI DUCT™ AND HVAC INSTALLATION ACCESSORIES CATALOG

Speedi Duct™ Products	2
Speedi Duct™ Benefits	
Starter Kit	
Starter Kit XL	
Flex Hose Kit	4
Line Set Duct	4
Components	
HVAC Installation Accessories	
Condenser Support	
Base Pad	
Mount Block	
Mount Block End Cap	
Wall Support	
Condenser Bracket	
Wall Sleeve	
Drain Hose	11
Drain Hose Y-Connection	

Speedi Duct™ and SpinFix™ are trademarks owned by Castel Engineering sa.

1/2016 © Castel Engineering sa – Belgium. All pictures and drawings in this litterature are for illustration purposes only.

Data may change without prior notice and are subject to tolerances. Castel Engineering sa, its Affiliates and its Distributors cannot be held liable for typographical errors, layout errors or technical misinformation contained herein.


For the most up-to-date product information, visit **littlegiant.com**.



#### SPEEDI DUCT™ BENEFITS

#### **AVAILABLE IN THREE SIZES**







3" / 70 mm 4" / 105 mm 6" / 150 mm

#### PROTECTS THE LINE SET

For most installations, the insulated line set and drain hose run along the exterior wall before passing through and connecting to the indoor unit. Line set insulation is particularly vulnerable to deterioration from climatic conditions and UV rays. As a result, the weakened material can be further damaged by birds and insects. Without proper protection, the insulation can be damaged and lose its insulating properties.

#### **COST AND ENERGY SAVINGS**

- Air conditioning and heat pump equipment does not operate properly when the line set becomes damaged, or when the insulation deteriorates to expose the piping underneath. The results of this damage are higher maintenance costs and a shortened lifespan of the unit. Speedi Duct™ protects the equipment and contributes to extending its life.
- Exposed line sets are less efficient, resulting in a system that uses more energy and costs more to operate. Speedi Duct™ protects line set insulation to maintain correct operating efficiency of the equipment.

#### **PAINTABLE**

Speedi Duct™ can be painted to blend with any exterior/interior color palette, making it practically disappear on the wall. In order to ensure good paint adhesion, it is recommended to follow the paint manufacturer's instructions for painting plastic (PVC, ASA, PP, PE).

#### **DESIGNED FOR BOTH UNITARY AND MINI-SPLIT UNITS**

- Speedi Duct™ includes a wide range of fittings that offer the professional installer a solution for the most difficult installation configurations, whether unitary, heat pump, or ductless mini-split equipment.
- The top and bottom sections are assembled with quality stainless steel screws that provide a very rigid and stable installation with no loose-fitting parts that could potentially make noise.
- Other line set duct covers have a rounded bottom that allows dust, insects, and debris from bird nests to accumulate. Speedi Duct™ utilizes a flat bottom, flush-fitting design that protects the line set and improves in-corner fit that eliminates unsightly gaps.

#### **5 STEPS FOR A ONE-MAN JOB**



1. Affix the bottom half of the fitting and duct to the wall (screws not included).



2. With a cable tie placed into the SpinFix™, insert and rotate it into the Speedi Duct™ rail.



3. Place the line set, drain hose, and control cable within the duct. Fasten the cable tie.



4. Snap on the top cover



5. Install the top fitting using the included stainless steel screws for a rigid assembly.



# STARTER KIT

- (3) 4' (1.22 m) Straight Duct
- (1) Duct End
- (1) Wall Cover
- (10) SpinFix<sup>™</sup> and Cable Ties
- (2) Unions
- (1) 45° to 90° Adjustable Flat Elbow

Model No.

D3-IKW

D4-IK

D4-IKW




4" / 105 mm

Ivory

White

4" / 105 mm



# STARTER KIT XL

Item No.

599600050

599600350

599600051

599600351

- (3) 4' (1.22 m) Line Set Duct
- (1) 39.4" (1 m) Flexible Hose
- (1) Wall Cover
- (1) Flex Hose Connector
- (2) Unions
- (1) End Cap
- (1) 90° Long Flat Elbow
- (1) Stainless Steel Clamp
- (10) SpinFix<sup>™</sup> and Cable Ties

2000	

3.0" / 75 mm

Item No.	Model No.	Sizo	Color	Dimei	nsions
item no.	Model No.	Size	COIOI	A	В
599600083	D3-IK-XL	3" / 70 mm	lvory	3" / 70 mm	2.6" / 65 mm
599600383	D3-IKW-XL	3 / /0	White	3 / 10 111111	2.0 / 03 111111
599600084	D4-IK-XL	4" / 105 mm	Ivory	4" / 105 mm	3" / 75 mm
599600384	D4-IKW-XL	4 / 103 111111	White	4 / 103 111111	וווווו כזן כ

	Α	
В		

3



# FLEX HOSE KIT

- (2) 39" (1 m) Flexible Hose
- (4) 2 Stainless Steel Clamps
- (4) 2 Flexible Hose Connectors
- (2) End Cap

Item No.	Model No.	Color	Designed For Use With
599600052	D3-FHK	lvory	3" Duct
599600352	D3-FHKW	White	3 Duct
599600053	D4-FHK	lvory	4" Duct
599600353	D4-FHKW	White	4 Duci



# LINE SET DUCT

- Straight line set duct
- Quick and easy installation
- Made of rigid PVC; withstands temperatures -4 to 140 °F (-20 to 60 °C) in static position (using SpinFix<sup>™</sup> and cable ties)
- Protects the line set against deterioration due to climatic conditions and helps to reduce energy consumption
- (3) Snap-lock SpinFix<sup>™</sup> are included with each 6.5' length (D3-S and D4-S only)

Item No.	Model No.	Size	Color	Dimensions		Length	Qty. (pcs).
iteiii no.	Model No.	3126	COIOI	A	A B		
599600001	D3-S	3" / 70 mm	lvory	3" / 70 mm	2.5" / 65 mm		6
599600301	D3-SW	3 / /0	White	3 / /U IIIIII	2.3 / 03 111111		0
599600002	D4-S	4" / 105 mm	lvory	4" / 105 mm	3" / 75 mm	6.5' / 2000 mm	<b>C</b>
599600302	D4-SW	4 / 103 111111	White	4 / 103 111111	) / /3	0.5 / 2000 111111	0
599600003	D6-S	6" / 1E0 mm	lvory	6" / 1E0 mm	7 2E" / 00 mm		г
599600303	D6-SW	6" / 150 mm	White	6" / ISU MM   3 /5" / XU MM			כ









Flex Hose Kit Installed



# COMPONENTS

#### **SPINFIX**<sup>TM</sup>

- Twist-motion locks into mounting rail and is easily repositioned
- SpinFix<sup>™</sup> and cable tie keep the line set in place during installation

Item No.	Model No.	Description	Qty. (bag)
599600047	D-SFCT-10	SpinFix™ and Cable Ties	10
599600048	D-SF-50	SpinFix™	50
599600049	D-CT-50	Cable Ties	50



#### **WALL COVER**

■ To cover through-wall opening

Item No.	Model No.	Size	Color	Qty. (pcs.)
599600008	D3-WC	3" / 70 mm	Ivory	
599600308	D3-WCW	3 / /0	White	
599600009	D4-WC	4" / 105 mm	Ivory	10
599600309	D4-WCW	4 / 103 111111	White	10
599600010	D6-WC	6" / 150 mm	Ivory	
599600310	D6-WCW	0 / 150 111111	White	



#### UNION

Item No.	Model No.	Size	Color	Qty. (pcs.)
599600026	D3-U	7" / 70 mm	Ivory	
599600326	D3-UW	3" / 70 mm	White	
599600027	D4-U	4" / 105 mm	Ivory	10
599600327	D4-UW	4 / 103111111	White	10
599600028	D6-U	6" / 150 mm	Ivory	
599600328	D6-UW	וווווו טכו / ט	White	



#### **SOFFIT COVER**

Item No.	Model No.	Size	Color	Qty. (pcs.)
599600006	D3-SI	3" / 70 mm	Ivory	
599600306	D3-SIW	3 / /0	White	10
599700007	D4-SI	4" / 105 mm	Ivory	10
599600307	D4-SIW	4 / 103 111111	White	



#### **FLAT ROSETTE**

■ The unique flat rosette enables the duct to be mounted flush with the wall while covering the opening for the line sets to pass through the ceiling

Item No.	Model No.	Size	Color	Qty. (pcs.)
599600041	D3-FR	7" / 70 mm	Ivory	
599600341	D3-FRW	3" / 70 mm	White	
599600042	D4-FR	4" / 105 mm	Ivory	10
599600342	D4-FRW	4 / 103 111111	White	10
599600043	D6-FR	6" / 150 mm	Ivory	
599600343	D6-FRW	0 / 150 111111	White	





# COMPONENTS

#### **ADJUSTABLE FLAT ELBOW**

- Adjustable between 45° and 90°
- Specific installation situations may require Speedi Duct™ to be connected in various angles; the adjustable flat bend is the flexible solution

Item No.	Model No.	Size	Color	Qty. (pcs.)
599600004	D3-AFB	7" / 70 mm	lvory	
599600304	D3-AFBW	3" / 70 mm	White	10
599600005	D4-AFB	4" / 105 mm	lvory	10
599600305	D4-AFBW	4" / 105 mm	White	



#### 90° FLAT BEND ELBOW

Item No.	Model No.	Size	Color	Qty. (pcs.)
599600011	D3-90FB	3" / 70 mm	Ivory	
599600311	D3-90FBW	3 / /0	White	
599600012	D4-90FB	4" / 105 mm	Ivory	10
599600312	D4-90FBW	4 / 103 111111	White	10
599600013	D6-90FB	6" / 150 mm	Ivory	
599600313	D6-90FBW	0 / 150 111111	White	



#### **45° FLAT BEND ELBOW**

Item No.	Model No.	Size	Color	Qty. (pcs.)
599600017	D3-45FB	7" / 70 mm	Ivory	
599600317	D3-45FBW	3" / 70 mm	White	
599600018	D4-45FB	4" / 105 mm	Ivory	10
599600318	D4-45FBW	4 / 103 111111	White	10
599600019	D6-45FB	6" / 150 mm	Ivory	
599600319	D6-45FBW	ρ / 150 mm	White	



#### 90° ELBOW BEND (OUTSIDE CORNER)

•	•			
Item No.	Model No.	Size	Color	Qty. (pcs.)
599600020	D3-90C	3" / 70 mm	Ivory	
599600320	D3-90CW	3 / /0	White	
599600021	D4-90C	4" / 105 mm	lvory	10
599600321	D4-90CW	4 / 103 111111	White	10
599600022	D6-90C	6" / 1E0 mm	lvory	
599600322	D6-90CW	6" / 150 mm	White	



#### 90° ELBOW BEND (INSIDE CORNER)

Item No.	Model No.	Size	Color	Qty. (pcs.)
599600023	D3-90IC	3" / 70 mm	Ivory	
599600323	D3-90ICW	3 / /0	White	
599600024	D4-90IC	4" / 105 mm	Ivory	10
599600324	D4-90ICW	4 / 103111111	White	10
599600025	D6-90IC	6" / 150 mm	Ivory	
599600325	D6-90ICW	6" / 150 mm	White	







# COMPONENTS

#### 90° LONG FLAT ELBOW

■ Ideal when bending the line set with a wider radius


Item No.	Model No.	Size	Color	Qty. (pcs.)
599600014	D3-LFB	3" / 70 mm	Ivory	
599600314	D3-LFBW	3 / /0	White	
599600015	D4-LFB	4" / 105 mm	Ivory	10
599600315	D4-LFBW	4 / 105 111111	White	10
599600016	D6-LFB	6" / 1E0 mm	Ivory	
599600316	D6-LFBW	6" / 150 mm	White	



#### T-JOINT

- For multi-split systems (reducer joints are required)
- To combine a 3" (70 mm) duct with a 4" (105 mm) duct; to combine a 4" (105 mm) duct with a 6" (150 mm) duct

Item No.	Model No.	Size	Color	Qty. (pcs.)
599600029	D4-TJ	4" / 10F mm	Ivory	
599600329	D4-TJW	4" / 105 mm	White	10
599600030	D6-TJ	6" / 150 mm	Ivory	10
599600330	D6-TJW	וווווו ווווו ווווו	White	





#### **REDUCER JOINT**

■ To combine with T-Joint

Item No.	Model No.	Size	Color	Qty. (pcs.)
599600033	D34-RJ	3" / 70 mm -	Ivory	
599600333	D34-RJW	4" / 105 mm	White	10
599600034	D46-RJ	4" / 105 mm -	Ivory	10
599600334	D46-RJW	6" / 150 mm	White	

NOTE: D34-RJ used with D4-TJ to reduce D4-S and D3-S; D46-RJ used with D6-TJ to reduce D6-S and D4-S



#### **FLEX JOINT**

Available in ivory only


Item No.	N	lodel No.	Size	Color	Qty. (pcs.)
59960003	1	D3-FJ	3" / 70 mm	lyony	10
59960003	2	D4-FJ	4" / 105 mm	lvory	10

NOTE: The flexible (PE) is paintable in a rigid installed position, but requires specific attention of the paint manufacturer's recommendations for painting on PE plastics



#### **DUCT CAP**

Item No.	Model No.	Size	Color	Qty. (pcs.)
599600038	D3-C	3" / 70 mm	Ivory	
599600338	D3-CW	3 / /0	White	
599600039	D4-C	4" / 105 mm	Ivory	10
599600339	D4-CW	4 / 103111111	White	10
599600040	D6-C	6" / 150 mm	Ivory	
599600340	D6-CW	וווווו טכו / ט	White	





# COMPONENTS

# **DUCT END**

Item No.	Model No.	Size	Color	Qty. (pcs.)
599600035	D3-E	3" / 70 mm	Ivory	
599600335	D3-EW	3 / /0	White	
599600036	D4-E	4" / 105 mm	Ivory	10
599600336	D4-EW	4 / 103111111	White	10
599600037	D6-E	6" / 150 mm	lvory	
599600337	D6-EW	0 / 150 111111	White	





#### WALL ROSETTE

Item No.	Model No.	Size	Color	Qty. (pcs.)
599600044	D3-WR	3" / 70 mm	Ivory	
599600344	D3-WRW	3 / /0	White	
599600045	D4-WR	4" / 105 mm	Ivory	10
599600345	D4-WRW	4 / 103111111	White	10
599600046	D6-WR	6" / 150 mm	Ivory	
599600346	D6-WRW	וווווו טכו / ט	White	













#### HVAC INSTALLATION ACCESSORIES - CONDENSER SUPPORT

#### BASE PAD

- 4" x 4" x 14" (100 x 100 x 355 mm); 4" x 4" x 17" (100 x 100 x 432 mm)
- 220 lbs (100 kg) maximum allowable spread load capacity per item\*
- Mounting bolts and adjusting nuts included
- One set includes two base pads and mounting hardware



NOTE: Maximum load weight does not take into account any safety factors

#### MOUNT BLOCK

- 4" x 4" x 14" (100 x 100 x 355 mm); 4" x 4" x 17" (100 x 100 x 432 mm); 4" x 4" x 36" (100 x 100 x 914 mm)
- 1000 lbs (450 kg) maximum allowable spread load capacity per item\*
- Mounting bolts and nuts included
- Shock absorbent
- One set includes two mount blocks and mounting hardware

Item No.	Model No.	Length	Color	Qty. (sets)
599600057	MBW-14	13.8" / 350 mm		6
599600058	MBW-17	17.7" / 450 mm	White	6
599600059	MBW-36	39.4" / 1000 mm		1

NOTE: Maximum load weight does not take into account any safety factors







#### MOUNT BLOCK END CAP

- 4" x 4" (100 mm x 100 mm)
- End cap for mount block
- Quick and easy installation
- One set includes four pieces

Item No.	Model No.	Size	Color	Qty. (pcs.)
599600060	MBW-C	4" x 4" / 100 x 100 mm	Ivory	4









# HVAC INSTALLATION ACCESSORIES - WALL SUPPORT

# CONDENSER BRACKET

- Quick and easy to install
- Pre-assembled with one screw
- Reinforced two-point assembly
- Bracket arms can be easily adjusted via a unique sliding nut-holder
- Powder coated galvanized steel
- Supplied with crossbar mounting kit, anti-vibration dampers, and adjusters for easy leveling on uneven wall surfaces



	Item No.	Model No.	Dimensions			Max. Load Weight
			Horizontal	Vertical	Crossbar	(lb / kg)*
	599600061	WB-18	17.75" / 450 mm	15.75" / 400 mm	3' / 960 mm	176 + 176 / 80 + 80*
Ī	599600062	WB-21	21" / 530 mm	15.75 / 400 111111	3 / 900 111111	1/0 + 1/0 / 80 + 80

\*It is your responsibility to choose and use the appropriate tools and materials that ensure the final installation is in compliance with all national, state, local, and environmental regulations, and that safety factors are appropriate for your intended application of 176 lb (80 kg) per arm. Maximum load weight does not take into account any safety factors.





# Little GIANT.

#### HVAC INSTALLATION ACCESSORIES - HOSE AND CONNECTIONS

# WALL SLEEVE

- Protects line set insulation, electrical cable, and drain hose from damage during installation and afterward
- The collar covers indoor opening imperfections
- Cut to adjust to wall thickness, between 4" (100 mm) and 13.78" (350 mm)
- The hole should be made with a 2-1/2" (64 mm) hole saw

Item No.	Model No.	Qty. (pcs.)	
599600054	D-WS	10	



Without a wall sleeve, the insulation and drain hose is easily damaged







Wall sleeve and drain hose correctly installed

# DRAIN HOSE

- Standard ivory color
- Hose length 164' (50 m)
- Regular cut-marks
- Connects to 5/8" (16 mm), 11/16" (18 mm), and 3/4" (20 mm) systems

Model No.	Item No.	Connections	Color	Qty. (roll)
DH-1	599600065	5/8" - 11/16" - 3/4" / 16 mm - 18 mm - 20 mm	lvory	1

# DRAIN HOSE Y-CONNECTION

- Connects two DH-1 drain hoses into one
- Useful in multi-split installations









NOTES	



# Little GIANT®

