


HOME REFINE MENTS

003908 | J7®

UNDERMOUNT STAINLESS STEEL KITCHEN SINK



Specifications

Model	003908
Collection	J7®
Bowl dimensions	30" × 16" × 10"
Overall dimensions	31 1/2" × 17 1/2" × 10"
Recommended cabinet	36"

Recommended accessories

Drain	100082
Grid	200307
Colander SmartStation	205017
Colander SmartStation	205023
Bin SmartStation	205026
Tray SmartStation	205032
Cutting board SmartStation	210051
Drying Rack SmartStation	215006

Features

- Handcrafted in Canada
- Commercial quality stainless steel - 16 ga thickness
- Corrosion resistant material - 304 series (18/10)
- Environmentally friendly product, 100% recyclable
- Elegant no. 4 brushed finish that matches the appliances
- Highly efficient sound deadening pads
- Practical flat sink bottom and straight bowl sides that maximize available space in the bowl
- Stylish and functional bowl bottom grooves that facilitate water drainage
- Rear 3-1/2" drain placement
- Certifications: ASME A112.19.3, CSA B45.0, CSA B45.4

Warranty

Home Refinements offers a LIMITED LIFETIME WARRANTY on the fixed components of its stainless steel sinks against defects of material and workmanship. For further details on our product warranty, please refer to our catalog or Web site.