

Indoor/Outdoor Tank Alarm

VERSA'LARM™ I/O

Leading Edge Design



Dual Rated for either Indoor or Outdoor Use

- ▶ Type 1–Indoor use.
- ▶ Type 4X–Waterproof against pressurized wash-downs for outdoor use.

High Integrity Design

- ▶ Auto-reset feature automatically resets buzzer when alarm condition clears.


Environmentally Safe

- ▶ Patented mechanical float switch eliminates hazardous mercury.



Applications

- ▶ Lift pump chambers
- ▶ Holding tanks
- ▶ Sump pump basins
- ▶ Water tanks
- ▶ Septic tanks



The Versalarm™ I/O is powered by 120 VAC. When the float switch closes the buzzer and light will be activated. Pressing the silence button silences the buzzer. When the alarm condition is cleared, the system automatically resets itself.

Features

Automatic Buzzer Reset

Eliminates errors

Red Polycarbonate Beacon

High visibility

Alarm Buzzer

Loud 100 db warble

Terminal Block

Fast connections

Fuse – 1 Amp

Protects internal wiring

Entire System Dual Rated Type 1 and 4X

Indoor or outdoor use

Test/Silence Switches

Easy service

Internal Wiring Diagram

Quick installation

3-Year Warranty

Guaranteed performance

UL Listed

Listed by UL for safety and performance



Leading Edge Control Products

Alarm Systems

Control Panels

Float Switches

Leak Detection Systems

Indoor/Outdoor Tank Alarm


VERSA'LARM™ I/O

Specifications




Versa'larm™ I/O

Primary Power: 120 VAC, 50/60 Hz
Watts: 15 watts
Fuse: 1 amp fast-acting type AGC
Buzzer: 100 db warble
Switch: 120 VAC, 1 amp minimum
 (Signaling device) Single pole, single throw
Enclosure: PVC UL type 4X
System Rating: UL type 1 and 4X



Unimax™ Float

Electrical: 5 amps, 120/230VAC
Operating Temperature: 0-140 F
Cable: SJOW-flexible, 16 gauge, water resistant, rubber (CPE)
Float Housing: High impact PVC
Switch Arrangement: Single pole, single throw
Switching Differential: 10 degrees total



Order Numbers

Indoor / Outdoor Versa'larm™ I/O

Alarm is dual rated, Type I indoor and Type 4X outdoor and includes Auto Reset

Part Number	Description	Versa'larm™ I/O	Unimax™ Mechanical Float Switch
7031	Alarm panel only (no sensor)	X	
7004	Tank Alarm – High Level, 15' Cable	X	X
7032	Tank Alarm – High Level, 20' Cable	X	X
7033	Tank Alarm – Low Level, 15' Cable	X	X



Leading Edge Control Products

Alarm Systems

Control Panels

Float Switches

Leak Detection Systems

PO Box 827 • Hawley, MN 56549 • (218) 483-3034 • Fax (218) 483-3036 • www.alderonind.com