

NES Series

Water Softeners



The Right Condition for Your Water



LOADED WITH FEATURES



EASY TO PROGRAM

MERELY PUSH THE BUTTON TO SET THE TIME OF DAY AND HARDNESS...YOUR DONE! CONTROL VALVE BUILT FOR MINIMUM WATER AND SALT USAGE.

OPTIONAL ADVANCE PROGRAMMING

THE ADJUSTMENT OF EACH CYCLE DURATION; REGENERATION TIME; AND DAYS OVER-RIDE

RUGGED RESIN

FIBERGLASS CONSTRUCTION, WILL NEVER RUST OR CORRODE

VORTEX DISTRIBUTOR

SAFETY BRINE VORTED DISTRI

SCRUBS THE RESIN EACH
REGENERATION TO EXTEND
THE LIFE OF THE SOFTENER

SALT SHELF

ELIMINATES MESSY

OVERFLOW SHOULD A

MALFUNCTION OCCUR

ALLOWS THE USE OF INEXPENSIVE SALT AND REDUCES THE CHANCE OF SALT BRIDGING AND MUSHING

SELF LEVELING BASE

COMPENSATES FOR UNLEVEL FLOOR

EASY TO INSTALL... EASY TO SERVICE



QUICK RELEASE DRAIN FITTING

NO THREADS TO LEAK.
MERELY PULL CLIP TO
REMOVE DRAIN FITTING





PUSH-IN BRINE LINE FITTING

ELIMINATES CONFUSING FERRELS AND NUTS THAT CAN CAUSE LEAKS



STAINLESS STEEL BYPASS

OPERATES WITH SINGLE HANDLE. 3/4" FEMALE THREADS


NES SERIES SPECIFICATIONS

Model Number	Grain Capacity		Service Flow Rate (gpm)		Salt Storage	Dimensions *Inlet Height				Pipe Size
	Max.	Min.	Peak	Service	(lbs.)	Α	*B	O	D	Size
NES-0.75-S	22,500	21,000	12	6	200	52"	45.75"	23"	14"	3/4" or 1" (-1S suffix)
NES-1-S	30,000	24,000	13	8	200	56"	49.75"	24"	14"	
NES-1.5-S	45,000	33,000	13	10	200	62"	56"	25"	14"	
NES-2-S	60,000	48,000	14	12	200	56"	49.75"	27"	14"	
NES-2.5-S	75,000	48,500	15	14	200	62"	56"	32"	18"	

SPACE-MAKER

Model Number	Grain Capacity		Service Flow Rate (gpm)		Salt Storage	Dimensions *Inlet Height				Pipe
	Max.	Min.	Peak	Service	(lbs.)	Α	*B	С	D	Size
NECS-0.75-S	22,500	21,000	14	6	150	43"	36.50"	23"	13"	3/4"
NECS-1-S	30,000	24,000	14	8	150	43"	36.50"	23"	13"	3/4"

NOTE: Service flow rate of control valve (only) is 20gpm @ 15 psig drop.





Enjoy all the benefits of soft water: cleaner laundry, sparkling