

LOWELL DESIGN GUIDE

SOCKET WRENCHES

HANDLES

Square sockets

[illegible]

Hex sockets

[illegible]

Double Square sockets

[illegible]

Triple Square sockets

[illegible]

Double hex sockets

	DS-1	DS-2	DS-3	DS-4	DS-6
DS-1					
DS-2					
DS-3					
DS-4					
DS-6					

Pentagon sockets

52, 52F, 52QR, 53, 53F, 53QR, 152, 152F, 252F	■	■	■
---	---	---	---

LOWELL DESIGN GUIDE

SOCKET WRENCHES

HANDLES

Square sockets

50, 50QR, 51, 51QR, 150, 151, 158, 564QR
52, 52F, 52QR, 53, 53F, 53QR, 152, 152F, 252F
54, 55
56
58
60

Hex sockets

50, 50QR, 51, 51QR, 150, 151, 158, 564QR
52, 52F, 52QR, 53, 53F, 53QR, 152, 152F, 252F
54, 55
56
58
60

Double Square sockets

50, 50QR, 51, 51QR, 150, 151, 158, 564QR
52, 52F, 52QR, 53, 53F, 53QR, 152, 152F, 252F

Triple Square sockets


50T, 51T, 150T, 151T

Double hex sockets

DS-5
DS-7
DS-8
DS-9


Pentagon sockets

52, 52F, 52QR, 53, 53F, 53QR, 152, 152F, 252F



LOWELL DESIGN GUIDE

SOCKET WRENCHES



Lengths	8"	10"	12"	15"	15 1/2"	20"	24"	36"	43"	60"
Models	158	50	51	52	152	53	54	55	58	60
		50QR	51QR	52F	152F	53F		56		
		50T	51T	52QR	252F*	53QR				
		150	151	564QR						
		150T	151T							
			DS-1							
			DS-2							
			DS-3							
			DS-4							
			DS-5							
			DS-6							
			DS-7							
			DS-8							
			DS-9							

* 252F is a double handled unit

LOWELL DESIGN GUIDE

SOCKET WRENCHES

150 SERIES Socket Wrenches

Model	P/N Handle Only	Nominal Length		Weight		Socket Openings		P/N	P/N Assembly
								Socket	
		IN	MM	LB	KG	IN	MM	Only	
150	87901	10	254	2	0,91	5/8 SQ		94610	87901/94610
						11/16 SQ		94611	87901/94611
						3/4 SQ		94612	87901/94612
						1 SQ		94616	87901/94616
						1 1/16 SQ		94617	87901/94617
						1 1/8 SQ		94618	87901/94618
						1 1/4 SQ		94620	87901/94620
							16 SQ	M4616	87901/M4616
							17 SQ	M4617	87901/M4617
							19 SQ	M4619	87901/M4619
							22 SQ	M4622	87901/M4622
							24 SQ	M4624	87901/M4624
							25 SQ	M4625	87901/M4625
							27 SQ	M4627	87901/M4627
							28 SQ	M4628	87901/M4628
							30 SQ	M4630	87901/M4630
							32 SQ	M4632	87901/M4632
						5/8 HEX		94710	87901/94710
						3/4 HEX		94712	87901/94712
						7/8 HEX		94714	87901/94714
						15/16 HEX		94715	87901/94715
						1 HEX		94716	87901/94716
						1 1/16 HEX		94717	87901/94717
						1 1/8 HEX		94718	87901/94718
						1 1/4 HEX		94720	87901/94720
							16 HEX	M4716	87901/M4716
							17 HEX	M4717	87901/M4717
							19 HEX	M4719	87901/M4719
							22 HEX	M4922	87901/M4922
							24 HEX	M4724	87901/M4724
							25 HEX	M4725	87901/M4725
							27 HEX	M4727	87901/M4727
							28 HEX	M4728	87901/M4728
							30 HEX	M4730	87901/M4730
							32 HEX	M4730	87901/M4730
151	88901	12	305	2 1/8	0,96	5/8 SQ		94610	88901/94610
						11/16 SQ		94611	88901/94611
						3/4 SQ		94612	88901/94612
						1 SQ		94616	88901/94616
						1 1/16 SQ		94617	88901/94617
						1 1/8 SQ		94618	88901/94618
						1 1/4 SQ		94620	88901/94620
							16 SQ	M4616	88901/M4616
							17 SQ	M4617	88901/M4617
							19 SQ	M4619	88901/M4619

**HANDLE, SOCKET AND
ASSEMBLY PART NUMBERS**

Lowell Corporation
www.lowellcorp.com
customerservice@lowellcorp.com

LOWELL DESIGN GUIDE

SOCKET WRENCHES

I 50 SERIES Socket Wrenches

Model	P/N Handle Only	Nominal				Socket Openings		P/N Socket Only	P/N Assembly	
		Length		Weight		IN	MM			
		IN	MM	LB	KG					
151	88901	12	305	2 1/8	0,96		22 SQ	M4622	88901/M4622	
							24 SQ	M4624	88901/M4624	
							25 SQ	M4625	88901/M4625	
							27 SQ	M4627	88901/M4627	
							28 SQ	M4628	88901/M4628	
							30 SQ	M4630	88901/M4630	
							32 SQ	M4632	88901/M4632	
						5/8	HEX		94710	88901/94710
						3/4	HEX		94712	88901/94712
						7/8	HEX		94714	88901/94714
						15/16	HEX		94715	88901/94715
						1	HEX		94716	88901/94716
						1 1/16	HEX		94717	88901/94717
						1 1/8	HEX		94718	88901/94718
						1 1/4	HEX		94720	88901/94720
							16 HEX	M4716	88901/M4716	
							17 HEX	M4717	88901/M4717	
							19 HEX	M4719	88901/M4719	
							22 HEX	M4922	88901/M4922	
							24 HEX	M4724	88901/M4724	
							25 HEX	M4725	88901/M4725	
							27 HEX	M4727	88901/M4727	
							28 HEX	M4728	88901/M4728	
							30 HEX	M4730	88901/M4730	
							32 HEX	M4730	88901/M4730	
158	86901	8	204	1 3/4	0,79		5/8 SQ	94610	86901/94610	
							11/16 SQ	94611	86901/94611	
							3/4 SQ	94612	86901/94612	
							1 SQ	94616	86901/94616	
							1 1/16 SQ	94617	86901/94617	
							1 1/8 SQ	94618	86901/94618	
							1 1/4 SQ	94620	86901/94620	
							16 SQ	M4616	86901/M4616	
							17 SQ	M4617	86901/M4617	
							19 SQ	M4619	86901/M4619	
							22 SQ	M4622	86901/M4622	
							24 SQ	M4624	86901/M4624	
							25 SQ	M4625	86901/M4625	
							27 SQ	M4627	86901/M4627	
							28 SQ	M4628	86901/M4628	
							30 SQ	M4630	86901/M4630	
							32 SQ	M4632	86901/M4632	
							5/8 HEX	94710	86901/94710	
							3/4 HEX	94712	86901/94712	
							7/8 HEX	94714	86901/94714	

**HANDLE, SOCKET AND
ASSEMBLY PART NUMBERS**

Lowell Corporation
www.lowellcorp.com
customerservice@lowellcorp.com

LOWELL DESIGN GUIDE

SOCKET WRENCHES

I 50 SERIES Socket Wrenches

Model	P/N Handle Only	Nominal Length		Weight		Socket Openings		P/N	P/N Assembly
								Socket	
		IN	MM	LB	KG	IN	MM	Only	
158	86901	8	204	1 3/4	0,79	15/16 HEX		94715	86901/94715
						1 HEX		94716	86901/94716
						1 1/16 HEX		94717	86901/94717
						1 1/8 HEX		94718	86901/94718
						1 1/4 HEX		94720	86901/94720
							16 HEX	M4716	86901/M4716
							17 HEX	M4717	86901/M4717
							19 HEX	M4719	86901/M4719
							22 HEX	M4922	86901/M4922
							24 HEX	M4724	86901/M4724
							25 HEX	M4725	86901/M4725
							27 HEX	M4727	86901/M4727
							28 HEX	M4728	86901/M4728
							30 HEX	M4730	86901/M4730
							32 HEX	M4730	86901/M4730
152	15201	15 3/4	400	3 3/4	1,70	5/8 SQ		95610	15201/95610
						1 1/8 SQ		95618	15201/95618
						1 1/4 SQ		95620	15201/95620
						1 5/16 SQ		95621	15201/95621
						1 1/2 SQ		95624	15201/95624
							24 SQ	M5624	15201/M5624
							30 SQ	M5630	15201/M5630
						13/16 HEX		95713	15201/95713
						7/8 HEX		95714	15201/95714
						15/16 HEX		95715	15201/95715
						1 HEX		95716	15201/95716
						1 1/16 HEX		95717	15201/95717
						1 1/8 HEX		95718	15201/95718
						1 3/16 HEX		95719	15201/95719
						1 1/4 HEX		95720	15201/95720
						1 5/16 HEX		95721	15201/95721
						1 7/16 HEX		95723	15201/95723
						1 1/2 HEX		95724	15201/95724
						1 5/8 HEX		95726	15201/95726
							22 HEX	M5722	15201/M5722
							24 HEX	M5724	15201/M5724
							25 HEX	M5725	15201/M5725
							27 HEX	M5727	15201/M5727
							28 HEX	M5728	15201/M5728
							30 HEX	M5730	15201/M5730
							32 HEX	M5732	15201/M5732
							33 HEX	M5733	15201/M5733
							36 HEX	M5736	15201/M5736
							38 HEX	M5738	15201/M5738
							41 HEX	M5741	15201/M5741

**HANDLE, SOCKET AND
ASSEMBLY PART NUMBERS**

Lowell Corporation
www.lowellcorp.com
customerservice@lowellcorp.com

LOWELL DESIGN GUIDE

SOCKET WRENCHES

I 50 SERIES Socket Wrenches

Model	P/N Handle Only	Nominal				Socket Openings		P/N Socket Only	P/N Assembly
		Length		Weight		IN	MM		
		IN	MM	LB	KG				
I 52	I 5201	15 ¾	400	3 ¾	1,70		50 HEX	M5750	I 5201/M5750

LOWELL DESIGN GUIDE

SOCKET WRENCHES

50 SERIES Socket Wrenches

Model	P/N Handle Only	Nominal Length		Weight		Socket Openings		P/N Socket Only	P/N Assembly
		IN	MM	LB	KG	IN	MM		
50	50901	10	254	2	0,91	5/8 SQ		94610	50901/94610
						11/16 SQ		94611	50901/94611
						3/4 SQ		94612	50901/94612
						1 SQ		94616	50901/94616
						1 1/16 SQ		94617	50901/94617
						1 1/8 SQ		94618	50901/94618
						1 1/4 SQ		94620	50901/94620
							16 SQ	M4616	50901/M4616
							17 SQ	M4617	50901/M4617
							19 SQ	M4619	50901/M4619
							22 SQ	M4622	50901/M4622
							24 SQ	M4624	50901/M4624
							25 SQ	M4625	50901/M4625
							27 SQ	M4627	50901/M4627
							28 SQ	M4628	50901/M4628
							30 SQ	M4630	50901/M4630
							32 SQ	M4632	50901/M4632
						5/8 HEX		94710	50901/94710
						3/4 HEX		94712	50901/94712
						7/8 HEX		94714	50901/94714
						15/16 HEX		94715	50901/94715
						1 HEX		94716	50901/94716
						1 1/16 HEX		94717	50901/94717
						1 1/8 HEX		94718	50901/94718
						1 1/4 HEX		94720	50901/94720
							16 HEX	M4716	50901/M4716
							17 HEX	M4717	50901/M4717
							19 HEX	M4719	50901/M4719
							22 HEX	M4922	50901/M4922
							24 HEX	M4724	50901/M4724
							25 HEX	M4725	50901/M4725
							27 HEX	M4727	50901/M4727
							28 HEX	M4728	50901/M4728
							30 HEX	M4730	50901/M4730
							32 HEX	M4730	50901/M4730
51	51901	12	305	2 1/8	0,96	5/8 SQ		94610	51901/94610
						11/16 SQ		94611	51901/94611
						3/4 SQ		94612	51901/94612
						1 SQ		94616	51901/94616
						1 1/16 SQ		94617	51901/94617
						1 1/8 SQ		94618	51901/94618
						1 1/4 SQ		94620	51901/94620
							16 SQ	M4616	51901/M4616
							17 SQ	M4617	51901/M4617
							19 SQ	M4619	51901/M4619
							22 SQ	M4622	51901/M4622

**HANDLE, SOCKET AND
ASSEMBLY PART NUMBERS**

Lowell Corporation
www.lowellcorp.com
customerservice@lowellcorp.com

LOWELL DESIGN GUIDE

SOCKET WRENCHES

50 SERIES Socket Wrenches

Model	P/N Handle		Nominal				Socket Openings		P/N Socket	
	Only		Length		Weight				Only	P/N Assembly
			IN	MM	LB	KG	IN	MM		
51	51901		12	305	2 1/8	0,96		24 SQ	M4624	51901/M4624
								25 SQ	M4625	51901/M4625
								27 SQ	M4627	51901/M4627
								28 SQ	M4628	51901/M4628
								30 SQ	M4630	51901/M4630
								32 SQ	M4632	51901/M4632
							5/8 HEX		94710	51901/94710
							3/4 HEX		94712	51901/94712
							7/8 HEX		94714	51901/94714
							1 5/16 HEX		94715	51901/94715
							1 HEX		94716	51901/94716
							1 1/16 HEX		94717	51901/94717
							1 1/8 HEX		94718	51901/94718
							1 1/4 HEX		94720	51901/94720
								16 HEX	M4716	51901/M4716
								17 HEX	M4717	51901/M4717
								19 HEX	M4719	51901/M4719
								22 HEX	M4922	51901/M4922
								24 HEX	M4724	51901/M4724
								25 HEX	M4725	51901/M4725
								27 HEX	M4727	51901/M4727
								28 HEX	M4728	51901/M4728
								30 HEX	M4730	51901/M4730
								32 HEX	M4730	51901/M4730
52	52901		15	382	4 1/8	1,87	5/8 SQ		95610	52901/95610
							1 1/8 SQ		95618	52901/95618
							1 1/4 SQ		95620	52901/95620
							1 5/16 SQ		95621	52901/95621
							1 1/2 SQ		95624	52901/95624
								24 SQ	M5624	52901/M5624
								30 SQ	M5630	52901/M5630
							1 3/16 HEX		95713	52901/95713
							7/8 HEX		95714	52901/95714
							1 5/16 HEX		95715	52901/95715
							1 HEX		95716	52901/95716
							1 1/16 HEX		95717	52901/95717
							1 1/8 HEX		95718	52901/95718
							1 3/16 HEX		95719	52901/95719
							1 1/4 HEX		95720	52901/95720
							1 5/16 HEX		95721	52901/95721
							1 7/16 HEX		95723	52901/95723
							1 1/2 HEX		95724	52901/95724
							1 5/8 HEX		95726	52901/95726
								22 HEX	M5722	52901/M5722
								24 HEX	M5724	52901/M5724
								25 HEX	M5725	52901/M5725

**HANDLE, SOCKET AND
ASSEMBLY PART NUMBERS**

Lowell Corporation
www.lowellcorp.com
customerservice@lowellcorp.com

LOWELL DESIGN GUIDE

SOCKET WRENCHES

50 SERIES Socket Wrenches

P/N Handle		Nominal				P/N Socket			
Model	Only	Length		Weight		Socket Openings		Only	P/N Assembly
		IN	MM	LB	KG	IN	MM		
52	52901	15	382	4 1/8	1,87		27 HEX	M5727	52901/M5727
							28 HEX	M5728	52901/M5728
							30 HEX	M5730	52901/M5730
							32 HEX	M5732	52901/M5732
							33 HEX	M5733	52901/M5733
							36 HEX	M5736	52901/M5736
							38 HEX	M5738	52901/M5738
							41 HEX	M5741	52901/M5741
							50 HEX	M5750	52901/M5750
53	53901	20	508	5	2,27		5/8 SQ	95610	53901/95610
							3/4 SQ	95612	53901/95612
							7/8 SQ	95614	53901/95614
							1 SQ	95616	53901/95616
							1 1/16 SQ	95617	53901/95617
							1 1/8 SQ	95618	53901/95618
							1 3/16 SQ	95619	53901/95619
							1 1/4 SQ	95620	53901/95620
							1 5/16 SQ	95621	53901/95621
							1 1/2 SQ	95624	53901/95624
							24 SQ	M5624	53901/M5624
							25 SQ	M5625	53901/M5625
							27 SQ	M5627	53901/M5627
							30 SQ	M5630	53901/M5630
							32 SQ	M5632	53901/M5632
							33 SQ	M5633	53901/M5633
							36 SQ	M5636	53901/M5636
							13/16 HEX	95713	53901/95713
							7/8 HEX	95714	53901/95714
							15/16 HEX	95715	53901/95715
							1 HEX	95716	53901/95716
							1 1/16 HEX	95717	53901/95717
							1 1/8 HEX	95718	53901/95718
							1 3/16 HEX	95719	53901/95719
							1 1/4 HEX	95720	53901/95720
							1 5/16 HEX	95721	53901/95721
							1 7/16 HEX	95723	53901/95723
							1 1/2 HEX	95724	53901/95724
							1 5/8 HEX	95726	53901/95726
							22 HEX	M5722	53901/M5722
							24 HEX	M5724	53901/M5724
							25 HEX	M5725	53901/M5725
							27 HEX	M5727	53901/M5727
							28 HEX	M5728	53901/M5728
							30 HEX	M5730	53901/M5730
							32 HEX	M5732	53901/M5732
							33 HEX	M5733	53901/M5733

**HANDLE, SOCKET AND
ASSEMBLY PART NUMBERS**

Lowell Corporation
www.lowellcorp.com
customerservice@lowellcorp.com

LOWELL DESIGN GUIDE

SOCKET WRENCHES

50 SERIES Socket Wrenches

P/N Handle		Nominal				P/N Socket			
Model	Only	Length		Weight		Socket Openings		Only	P/N Assembly
		IN	MM	LB	KG	IN	MM		
53	53901	20	508	5	2,27		36 HEX	M5736	53901/M5736
							38 HEX	M5738	53901/M5738
							41 HEX	M5741	53901/M5741
							50 HEX	M5750	53901/M5750
54	54901	24	610	9 ¼	4,20		1 SQ	96616	54901/96616
							1 1/16 SQ	96617	54901/96617
							1 1/8 SQ	96618	54901/96618
							1 ¼ SQ	96620	54901/96620
							1 5/16 SQ	96621	54901/96621
							1 3/8 SQ	96622	54901/96622
							1 7/16 SQ	96823	54901/96823
							1 ½ SQ	96624	54901/96624
							1 5/8 SQ	96626	54901/96626
							1 11/16 SQ	96627	54901/96627
							1 13/16 SQ	96629	54901/96629
							1 7/8 SQ	96630	54901/96630
							2 SQ	96632	54901/96632
							25 SQ	M6625	54901/M6625
							28 SQ	M6628	54901/M6628
							30 SQ	M6630	54901/M6630
							32 SQ	M6632	54901/M6632
							34 SQ	M6634	54901/M6634
							38 SQ	M6638	54901/M6638
							46 SQ	M6646	54901/M6646
							47 SQ	M6647	54901/M6647
							50 SQ	M6650	54901/M6650
							55 SQ	M6655	54901/M6655
							1 HEX	96716	54901/96716
							1 1/16 HEX	96717	54901/96717
							1 1/8 HEX	96718	54901/96718
							1 ¼ HEX	96720	54901/96720
							1 5/16 HEX	96721	54901/96721
							1 3/8 HEX	96722	54901/96722
							1 7/16 HEX	96723	54901/96723
							1 ½ HEX	96724	54901/96724
							1 5/8 HEX	96726	54901/96726
							1 11/16 HEX	96727	54901/96727
							1 13/16 HEX	96729	54901/96729
							1 7/8 HEX	96730	54901/96730
							2 HEX	96732	54901/96732
							2 1/16 HEX	96733	54901/96733
							2 1/8 HEX	96734	54901/96734
							2 3/16 HEX	96735	54901/96735
							2 ¼ HEX	96736	54901/96736
							2 3/8 HEX	96738	54901/96738
							2 5/8 HEX	96742	54901/96742

**HANDLE, SOCKET AND
ASSEMBLY PART NUMBERS**

Lowell Corporation
www.lowellcorp.com
customerservice@lowellcorp.com

LOWELL DESIGN GUIDE

SOCKET WRENCHES

50 SERIES Socket Wrenches

Model	P/N Handle		Nominal				Socket Openings		P/N Socket	
	Only	Length	Weight		IN	MM	IN	MM	Only	P/N Assembly
			LB	KG						
54	54901	24	610	9 ¼	4,20			24 HEX	M6724	54901/M6724
								25 HEX	M6725	54901/M6725
								28 HEX	M6728	54901/M6728
								32 HEX	M6732	54910/M6732
								36 HEX	M6736	54901/M6736
								38 HEX	M6738	54901/M6738
								41 HEX	M6741	54901/M6741
								42 HEX	M6742	54901/M6742
								46 HEX	M6746	54901/M6746
								47 HEX	M6747	54901/M6747
								50 HEX	M6750	54901/M6750
								55 HEX	M6755	54901/M6755
								60 HEX	M6760	54901/M6760
55	55901	36	914	13	5,90			1 SQ	96616	55901/96616
								1 1/16 SQ	96617	55901/96617
								1 1/8 SQ	96618	55901/96618
								1 1/4 SQ	96620	55901/96620
								1 5/16 SQ	96621	55901/96621
								1 3/8 SQ	96622	55901/96622
								1 7/16 SQ	96623	55901/96623
								1 1/2 SQ	96624	55901/96624
								1 5/8 SQ	96626	55901/96626
								1 11/16 SQ	96627	55901/96627
								1 13/16 SQ	96629	55901/96629
								1 7/8 SQ	96630	55901/96630
								2 SQ	96632	55901/96632
								24 SQ	M6624	55901/M6624
								25 SQ	M6625	55901/M6625
								30 SQ	M6630	55901/M6630
								32 SQ	M6632	55901/M6632
								34 SQ	M6634	55901/M6634
								38 SQ	M6638	55901/M6638
								46 SQ	M6646	55901/M6646
								47 SQ	M6647	55901/M6647
								50 SQ	M6650	55901/M6650
								55 SQ	M6655	55901/M6655
								1 HEX	96716	55901/96716
								1 1/16 HEX	96717	55901/96717
								1 1/8 HEX	96718	55901/96718
								1 1/4 HEX	96720	55901/96720
								1 5/16 HEX	96721	55901/96721
								1 3/8 HEX	96722	55901/96722
								1 7/16 HEX	96823	55901/96823
								1 1/2 HEX	96724	55901/96724
								1 5/8 HEX	96726	55901/96726
								1 11/16 HEX	96727	55901/96727

**HANDLE, SOCKET AND
ASSEMBLY PART NUMBERS**

Lowell Corporation
www.lowellcorp.com
customerservice@lowellcorp.com

LOWELL DESIGN GUIDE

SOCKET WRENCHES

50 SERIES Socket Wrenches

Model	P/N Handle		Nominal				Socket Openings		P/N Socket	
	Only	Length	Weight		IN	MM	IN	MM	Only	P/N Assembly
			LB	KG						
55	55901	36	914	13	5,90		1 ¹³ / ₁₆ HEX		96729	55901/96729
							1 ⁷ / ₈ HEX		96730	55901/96730
							2 HEX		96732	55901/96732
							2 ¹ / ₁₆ HEX		96733	55901/96733
							2 ¹ / ₈ HEX		96734	55901/96734
							2 ³ / ₁₆ HEX		96735	55901/96735
							2 ¹ / ₄ HEX		96736	55901/96736
							2 ³ / ₈ HEX		96738	55901/96738
							2 ⁵ / ₈ HEX		96742	55901/96742
							24 HEX		M6724	55901/M6724
							25 HEX		M6725	55901/M6725
							28 HEX		M6728	55901/M6728
							32 HEX		M6732	55901/M6732
							36 HEX		M6736	55901/M6736
							38 HEX		M6738	55901/M6738
							41 HEX		M6741	55901/M6741
							42 HEX		M6742	55901/M6742
							46 HEX		M6746	55901/M6746
							47 HEX		M6747	55901/M6747
							50 HEX		M6750	55901/M6750
							55 HEX		M6755	55901/M6755
							60 HEX		M6760	55901/M6760
56	56901	36	914	24	10,9		1 ¹³ / ₁₆ SQ		97629	56901/97629
							2 SQ		97632	56901/97632
							2 ³ / ₁₆ SQ		97635	56901/97635
							2 ¹ / ₄ SQ		97636	56901/97636
							2 ³ / ₈ SQ		97638	56901/97638
							2 ¹ / ₂ SQ		97640	56901/97640
							3 SQ		97648	56901/97648
							50 SQ		M7650	56901/M7650
							60 SQ		M7660	56901/M7660
							65 SQ		M7665	56901/M7665
							1 ⁵ / ₈ HEX		97726	56901/97726
							1 ¹³ / ₁₆ HEX		97729	56901/97729
							1 ⁷ / ₈ HEX		97730	56901/97730
							2 HEX		97732	56901/97732
							2 ¹ / ₈ HEX		97734	56901/97734
							2 ³ / ₁₆ HEX		97735	56901/97735
							2 ¹ / ₄ HEX		97736	56901/97736
							2 ³ / ₈ HEX		97738	56901/97738
							2 ⁷ / ₁₆ HEX		97739	56901/97739
							2 ¹ / ₂ HEX		97740	56901/97740
							2 ⁹ / ₁₆ HEX		97741	56901/97741
							2 ⁵ / ₈ HEX		97742	56901/97742
							2 ³ / ₄ HEX		97744	56901/97744
							3 HEX		97748	56901/97748

**HANDLE, SOCKET AND
ASSEMBLY PART NUMBERS**

Lowell Corporation
www.lowellcorp.com
customerservice@lowellcorp.com

LOWELL DESIGN GUIDE

SOCKET WRENCHES

50 SERIES Socket Wrenches

P/N Handle		Nominal				P/N Socket			
Model	Only	Length		Weight		Socket Openings		Only	P/N Assembly
		IN	MM	LB	KG	IN	MM		
56	56901	36	914	24	10,9	3 1/8 HEX		97750	56901/97750
							41 HEX	M7741	56901/M7741
							46 HEX	M7746	56901/M7746
							50 HEX	M7750	56901/M7750
							55 HEX	M7755	56901/M7755
							60 HEX	M7760	56901/M7760
							65 HEX	M7765	56901/M7765
							70 HEX	M7770	56901/M7770
							80 HEX	M7780	56901/M7780
58	58901	43 1/2	1105	47	21,7	3 1/2 SQ		98656	58901/98656
							4 1/4 SQ	98668	58901/98668
							3 HEX	98748	58901/98748
							3 1/8 HEX	98750	58901/98750
							3 3/8 HEX	98754	58901/98754
							3 3/4 HEX	98760	58901/98760
							3 7/8 HEX	98762	58901/98762
							4 1/8 HEX	98766	58901/98766
							4 1/2 HEX	98772	58901/98772
							4 5/8 HEX	98774	58901/98774
							95 HEX	M8795	58901/M8795

LOWELL DESIGN GUIDE

SOCKET WRENCHES

50QR SERIES Quick Release Socket Wrenches

Model	P/N Handle	Nominal				Socket Openings		P/N Socket	P/N Assembly
	Only	Length		Weight		IN	MM	Only	
50QR	509Q1	10	254	2	0,91	$\frac{5}{8}$ SQ		94610	509Q1/94610
						$\frac{11}{16}$ SQ		94611	509Q1/94611
						$\frac{3}{4}$ SQ		94612	509Q1/94612
						1 SQ		94616	509Q1/94616
						$1 \frac{1}{16}$ SQ		94617	509Q1/94617
						$1 \frac{1}{8}$ SQ		94618	509Q1/94618
						$1 \frac{1}{4}$ SQ		94620	509Q1/94620
						16 SQ		M4616	509Q1/M4616
						17 SQ		M4617	509Q1/M4617
						19 SQ		M4619	509Q1/M4619
						22 SQ		M4622	509Q1/M4622
						24 SQ		M4624	509Q1/M4624
						25 SQ		M4625	509Q1/M4625
						27 SQ		M4627	509Q1/M4627
						28 SQ		M4628	509Q1/M4628
						30 SQ		M4630	509Q1/M4630
						32 SQ		M4632	509Q1/M4632
						$\frac{5}{8}$ HEX		94710	509Q1/94710
						$\frac{3}{4}$ HEX		94712	509Q1/94712
						$\frac{7}{8}$ HEX		94714	509Q1/94714
						$1 \frac{5}{16}$ HEX		94715	509Q1/94715
						1 HEX		94716	509Q1/94716
						$1 \frac{1}{16}$ HEX		94717	509Q1/94717
						$1 \frac{1}{8}$ HEX		94718	509Q1/94718
						$1 \frac{1}{4}$ HEX		94720	509Q1/94720
						16 HEX		M4716	509Q1/M4716
						17 HEX		M4717	509Q1/M4717
						19 HEX		M4719	509Q1/M4719
						22 HEX		M4922	509Q1/M4922
						24 HEX		M4724	509Q1/M4724
						25 HEX		M4725	509Q1/M4725
						27 HEX		M4727	509Q1/M4727
						28 HEX		M4728	509Q1/M4728
						30 HEX		M4730	509Q1/M4730
						32 HEX		M4730	509Q1/M4730
51QR	519Q1	12	305	$2 \frac{1}{8}$	0,96	$\frac{5}{8}$ SQ		94610	519Q1/94610
						$\frac{11}{16}$ SQ		94611	519Q1/94611
						$\frac{3}{4}$ SQ		94612	519Q1/94612
						1 SQ		94616	519Q1/94616
						$1 \frac{1}{16}$ SQ		94617	519Q1/94617
						$1 \frac{1}{8}$ SQ		94618	519Q1/94618
						$1 \frac{1}{4}$ SQ		94620	519Q1/94620
						16 SQ		M4616	519Q1/M4616
						17 SQ		M4617	519Q1/M4617
						19 SQ		M4619	519Q1/M4619
						22 SQ		M4622	519Q1/M4622

**HANDLE, SOCKET AND
ASSEMBLY PART NUMBERS**

Lowell Corporation
www.lowellcorp.com
customerservice@lowellcorp.com

LOWELL DESIGN GUIDE

SOCKET WRENCHES

50QR SERIES Quick Release Socket Wrenches

[illegible]

07/25
Lowell Corporation

www.lowellcorp.com

customerservice@lowellcorp.com

HANDLE, SOCKET AND ASSEMBLY PART NUMBERS

LOWELL DESIGN GUIDE

SOCKET WRENCHES

50QR SERIES Quick Release Socket Wrenches

P/N Handle		Nominal				P/N Socket			
Model	Only	Length		Weight		Socket Openings		Only	P/N Assembly
		IN	MM	LB	KG	IN	MM		
52QR	529Q1	15	382	4 1/8	1,87		27 HEX	M5727	529Q1/M5727
							28 HEX	M5728	529Q1/M5728
							30 HEX	M5730	529Q1/M5730
							32 HEX	M5732	529Q1/M5732
							33 HEX	M5733	529Q1/M5733
							36 HEX	M5736	529Q1/M5736
							38 HEX	M5738	529Q1/M5738
							41 HEX	M5741	529Q1/M5741
							50 HEX	M5750	529Q1/M5750
53QR	539Q1	20	508	5	2,27	5/8 SQ		95610	539Q1/95610
						1 1/8 SQ		95618	539Q1/95618
						1 1/4 SQ		95620	539Q1/95620
						1 5/16 SQ		95621	539Q1/95621
						1 1/2 SQ		95624	539Q1/95624
							24 SQ	M5624	539Q1/M5624
							30 SQ	M5630	539Q1/M5630
						13/16 HEX		95713	539Q1/95713
						7/8 HEX		95714	539Q1/95714
						15/16 HEX		95715	539Q1/95715
						1 HEX		95716	539Q1/95716
						1 1/16 HEX		95717	539Q1/95717
						1 1/8 HEX		95718	539Q1/95718
						1 3/16 HEX		95719	539Q1/95719
						1 1/4 HEX		95720	539Q1/95720
						1 5/16 HEX		95721	539Q1/95721
						1 7/16 HEX		95723	539Q1/95723
						1 1/2 HEX		95724	539Q1/95724
						1 5/8 HEX		95726	539Q1/95726
							22 HEX	M5722	539Q1/M5722
							24 HEX	M5724	539Q1/M5724
							25 HEX	M5725	539Q1/M5725
							27 HEX	M5727	539Q1/M5727
							28 HEX	M5728	539Q1/M5728
							30 HEX	M5730	539Q1/M5730
							32 HEX	M5732	539Q1/M5732
							33 HEX	M5733	539Q1/M5733
							36 HEX	M5736	539Q1/M5736
							38 HEX	M5738	539Q1/M5738
							41 HEX	M5741	539Q1/M5741
							50 HEX	M5750	539Q1/M5750
564QR	36925	15 1/2	394	3 1/4	1,48	5/8 SQ		94610	36925/94610
						11/16 SQ		94611	36925/94611
						3/4 SQ		94612	36925/94612
						1 SQ		94616	36925/94616
						1 1/16 SQ		94617	36925/94617
						1 1/8 SQ		94618	36925/94618

**HANDLE, SOCKET AND
ASSEMBLY PART NUMBERS**

Lowell Corporation
www.lowellcorp.com
customerservice@lowellcorp.com

LOWELL DESIGN GUIDE

SOCKET WRENCHES

50QR SERIES Quick Release Socket Wrenches

P/N Handle		Nominal				P/N Socket			
Model	Only	Length		Weight		Socket Openings		Only	P/N Assembly
		IN	MM	LB	KG	IN	MM		
564QR	36925	15 ½	394	3 ¼	1,48	1 ¼ SQ		94620	36925/94620
							16 SQ	M4616	36925/M4616
							17 SQ	M4617	36925/M4617
							19 SQ	M4619	36925/M4619
							22 SQ	M4622	36925/M4622
							24 SQ	M4624	36925/M4624
							25 SQ	M4625	36925/M4625
							27 SQ	M4627	36925/M4627
							28 SQ	M4628	36925/M4628
							30 SQ	M4630	36925/M4630
							32 SQ	M4632	36925/M4632
						5/8 HEX	94710	36925/94710	
						¾ HEX	94712	36925/94712	
						7/8 HEX	94714	36925/94714	
						15/16 HEX	94715	36925/94715	
						1 HEX	94716	36925/94716	
						1 1/16 HEX	94717	36925/94717	
						1 1/8 HEX	94718	36925/94718	
						1 ¼ HEX	94720	36925/94720	
						16 HEX	M4716	36925/M4716	
						17 HEX	M4717	36925/M4717	
						19 HEX	M4719	36925/M4719	
						22 HEX	M4922	36925/M4922	
						24 HEX	M4724	36925/M4724	
						25 HEX	M4725	36925/M4725	
						27 HEX	M4727	36925/M4727	
						28 HEX	M4728	36925/M4728	
						30 HEX	M4730	36925/M4730	
						32 HEX	M4730	36925/M4730	

LOWELL DESIGN GUIDE

SOCKET WRENCHES

50F SERIES Hydrant Wrenches

Model	P/N Handle	Nominal		Weight		Socket Openings		P/N Socket	P/N Assembly
	Only	Length						Only	
		IN	MM	LB	KG	IN	MM		
52F	52901	15	382	4 1/8	1,87	1 1/2 Pentagon		95824	52901/95824
						2 Pentagon		95832	52901/95832
						1 3/4 Pentagon		95828	52901/95828
						x 1 1/4 Square			
						combination			
						38 Pentagon		M5838	52901/M5838
						50 Pentagon		M5850	52901/M5850
						42 Pentagon x		M5842	52901/M5842
53F	53901	20	508	5	2,27	1 1/2 Pentagon		95824	53901/95824
						2 Pentagon		95832	53901/95832
						1 3/4 Pentagon		95828	53901/95828
						x 1 1/4 Square			
						combination			
						38 Pentagon		M5838	53901/M5838
						50 Pentagon		M5850	53901/M5850
						42 Pentagon x		M5842	53901/M5842
252	25201	32 1/2	826	6 1/4	2,84	1 1/2 Pentagon		95824	53901/95824
						2 Pentagon		95832	53901/95832
						1 3/4 Pentagon		95828	53901/95828
						x 1 1/4 Square			
						combination			
						38 Pentagon		M5838	53901/M5838
						50 Pentagon		M5850	53901/M5850
						42 Pentagon x		M5842	53901/M5842
Double Handle						32 Square			
						combination			
						38 Pentagon		M5838	53901/M5838
						50 Pentagon		M5850	53901/M5850
						42 Pentagon x		M5842	53901/M5842
						32 Square			
						combination			

LOWELL DESIGN GUIDE

SOCKET WRENCHES

DoubleShot Dual Socket Wrenches

								P/N	
P/N Handle		Nominal						Socket	
Model	Only	Length		Weight		Socket Openings		Only	P/N Assembly
		IN	MM	LB	KG	IN	MM		
DS-1	N/A	12	305	2 1/8	0,96	1 1/4 x 1 1/16	HEX	N/A	88901/94820
DS-2	N/A	12	305	2 1/8	0,96	1 1/8 x 15/16	HEX	N/A	88901/94818
DS-3	N/A	12	305	2 1/8	0,96	15/16 x 3/4	HEX	N/A	88901/94815
DS-4	N/A	12	305	2 1/8	0,96	7/8 x 3/4	HEX	N/A	88901/94814
DS-5	N/A	12	305	2 1/8	0,96		22 x 19 HEX	N/A	88901/94822
DS-6	N/A	12	305	2 1/8	0,96	1 1/8 x 1 1/16	HEX	N/A	88901/94817
DS-7	N/A	12	305	2 1/8	0,96		19 x 17 HEX	N/A	88901/M4819
DS-8	N/A	12	305	2 1/8	0,96		24 X 22 HEX	N/A	88901/M4824
DS-9	N/A	12	305	2 1/8	0,96		30 x 24 HEX	N/A	88901/M4830

LOWELL DESIGN GUIDE

SOCKET WRENCHES

Ratcheting Lineman's Wrenches

Model	P/N Handle		Nominal				P/N Socket	
	Only	Length	Weight		Socket Openings		Only	P/N Assembly
			IN	MM	LB	KG		
50D	50901	10	254	2	0,91	1 x 1 1/8 SQ	94818	50901/94818
50T	50901	10	254	2	0,91	3/4 x 1 x 1 1/8 SQ	94800	50901/94800
51D	51901	12	305	2 1/8	0,96	1 x 1 1/8 SQ	94818	51901/94818
51T	51901	12	305	2 1/8	0,96	3/4 x 1 x 1 1/8 SQ	94800	51901/94800
52	52901	15	382	4 1/8	1,87	1 1/8 x 1 1/4 SQ	95820	52901/95820
						1 5/16 SQ	95621	52901/95621
						1 5/16 x 1 7/16 SQ	95823	52901/95823
53	53901	20	508	5	2,27	1 1/8 x 1 1/4 SQ	95820	53901/95820
						1 5/16 SQ	95621	53901/95621
						1 5/16 x 1 7/16 SQ	95823	53901/95823
150D	87901	10	254	2	0,91	1 x 1 1/8 SQ	94818	87901/94818
150T	87901	10	254	2	0,91	3/4 x 1 x 1 1/8 SQ	94800	87901/94800
151D	88901	12	305	2 1/8	0,96	1 x 1 1/8 SQ	94818	88901/94818
151T	88901	12	305	2 1/8	0,96	3/4 x 1 x 1 1/8 SQ	94800	88901/94800
152	15201	15 3/4	400	3 3/4	1,70	1 1/8 x 1 1/4 SQ	95820	15201/95820
						1 1/8 x 1 5/16 SQ x 1 5/8 HEX	N/A	15226
						1 5/16 SQ	95621	15201/95621
						1 5/16 x 1 7/16 SQ	95823	15201/95823

LOWELL DESIGN GUIDE

SOCKET WRENCHES

Socket Sets

Model	P/N Set	Weight		Components	P/N Components
		LB	KG		
511	36511	7	3,18	Metal box	36901
				51QR handle	519Q1
				$\frac{7}{8}$ HEX socket	94714
				$\frac{15}{16}$ HEX socket	94715
				1 $\frac{1}{8}$ HEX socket	94718
				1 $\frac{1}{4}$ HEX socket	94720
512	36512	11	5,0	Metal box	36901
				51QR handle	519Q1
				$\frac{3}{4}$ HEX socket	94712
				$\frac{7}{8}$ HEX socket	94714
				$\frac{15}{16}$ HEX socket	94715
				1 $\frac{1}{16}$ HEX socket	94717
				1 $\frac{1}{8}$ HEX socket	94718
				1 $\frac{1}{4}$ HEX socket	94720
				Corporation stop socket	36915
				Buffalo spanner	36917
				$\frac{7}{8}$ "erie" Pentagon socket	36916
				8 $\frac{3}{4}$ " square male extension	36918
513	36513	13	5,90	Metal box	36906
				565QR head	36920
				560 torque wrench	36935
				$\frac{3}{4}$ HEX socket	94712
				$\frac{7}{8}$ HEX socket	94714
				$\frac{15}{16}$ HEX socket	94715
				1 $\frac{1}{16}$ HEX socket	94717
				1 $\frac{1}{8}$ HEX socket	94718
				1 $\frac{1}{4}$ HEX socket	94720
514	36514	11	5,0	Metal box	36901
				564QR handle	36925
				$\frac{3}{4}$ HEX socket	94712
				$\frac{7}{8}$ HEX socket	94714
				$\frac{15}{16}$ HEX socket	94715
				1 $\frac{1}{16}$ HEX socket	94717
				1 $\frac{1}{8}$ HEX socket	94718
521	36521	13 $\frac{1}{2}$	6,20	1 $\frac{1}{4}$ HEX socket	94720
				Metal box	36909
				52QR	529Q1
				1 $\frac{1}{4}$ HEX	95720
				1 $\frac{5}{16}$ HEX	95721
				1 $\frac{7}{16}$ HEX	95723
				1 $\frac{1}{2}$ HEX	95724
531	36531	14	6,40	1 $\frac{5}{8}$ HEX	95726
				Metal box	36909
				53QR	539Q1
				1 $\frac{1}{4}$ HEX	95720
				1 $\frac{5}{16}$ HEX	95721

LOWELL DESIGN GUIDE

SOCKET WRENCHES

Socket Sets

Model	P/N Set	Weight		Components	P/N Components
		LB	KG		
531	36531	14	6,40	1 7/16 HEX 1 1/2 HEX 1 5/8 HEX	95723 95724 95726
Extended Reach	23-09904-9900	9 3/4	4,42	Plastic box 51QR handle 7/8 HEX extended socket 15/16 HEX extended socket 1 1/16 HEX extended socket 1 1/8 HEX extended socket 1 1/4 HEX extended socket	23-09904-9906 519Q1 23-09904-9901 23-09904-9902 23-09904-9903 23-09904-9904 23-09904-9905
DS-IN	36DSI-N	9 1/8	4,14	Plastic box DS-1 DS-2 DS-4	23-16505-9990 88901/94820 88901/94818 88901/94814
DS-RP	36DSR-P	9 1/8	4,14	Plastic box DS-1 DS-2 DS-3	23-16505-9990 88901/94820 88901/94818 88901/94815
DS-LC	36DSL-C	9 1/8	4,14	Plastic box Blue handle Green handle Yellow handle	23-16505-9991 88901-1/94820-B 88901-2/94818-B 88901-6/94814-B
Valve Key	23-31106-9900	7 1/4	3,29	Plastic box Small socket Medium socket Large socket Bracket 3/8" bolt	23-31106-9996 23-31106-9901 23-31106-9902 23-31106-9903 23-31106-9907 23-31106-9908