

SPEC SHEET

LED Standard 24V Flexible Tape Light

- Durable and Bright LED
- Energy Efficient and Easy Installation
- Separates Every 12" via Pre-installed Modular Connectors
- Cuttable every 4" at the Cut Line & Linkable







Description

With many uses and applications, the 24V Standard LED Ribbon Tape is one of the most popular product in the display lighting industry. Step 1 Dezigns is offering the LED ribbon tape in 3 color temperatures and 4 color options. The Modular ribbon tape separates every 12" via installed molded plugs and is sold in 12" and cuttable every 4". Great for showcases, displays & back-lighting.

STVOFLT

Specifics

Wattage: 1.8w per ft.
Voltage: 24v DC
of Diodes: 18 per ft.

Color Temp.: 6000k Cool White,

4100k Natural White, 3000k Warm White,

Red, Green, Blue, or Amber

Brightness: 125 Lumen per ft.

Beam Angle: 120°

Size: 12" per section x 5/16" W x 1/16" H

Dimmable: Yes, with Dimmable Driver
Lifespan: ± 30,000 - 50,000 hours
Installation: Adhesive Back Tape


Power Supply: 24v DC Driver

Environment: Indoor Dry Location

Labels & Listing: UL Listed

Required Items: STVOFLCON Power Feed

24v DC LED Driver













STVOFLCONDC

24V LED Flexible Tape Light DC Power Feed

Length: 24"



STVOFLCON

24V LED Flexible Tape Light Hardwire **Power Feed**

Length: 24"



STVOFL12

24V LED Flexible Tape Light Joiner

Length: 12"



STVOFL06

24V LED Flexible Tape Light Joiner

Length: 6"



STVOFLTX

24V LED Flexible Tape Light X-Connector

- Can be modified to use as an X or T Connector (field cuttable)
- 1x Female and 3x Male



STVO12-T

LED Flex Tape T Connector

T Connector allows users to connect 3 pieces of LED Tape Light together without the hassle of solder or hard wire.



STDC-DC-ADPF

Female DC Hardwire Adapter Plug

Available in 2.1mm or 2.5mm



STDC-DC-ADPM

Male DC Hardwire Adaptor Plug

Available in 2.1mm or 2.5mm



STVOFLYCON

LED Flexible Tape Light Y-Connector DC Power Feed

Simply plug 2, 3, or 5 way Y Connector in the male end of your power supply to the female ends of the Y-Connector Power Feed.



STVOFLCONDC

Male - Female DC Extension Cable

- 2.1 mm Male-Female DC
- Lengths: Available in 3', 8', or 10'



STVOFLCONDC

Male - Male DC Extension Cable

- 2.1 mm Male-Male DC Extension Cable
- Length: 8'



STVOFLSWC

LED Flexible Tape Light In-Line Power Switch

Easily power on/off 24V LED Tape with this in line switch.



STDC-IL-DIM

In-Line Knob Dimmer Switch

Available in White or Black Finish

