

E12LED101

4.5W CRI 80 2700K 300 Lumens LED Filament


Dimmable

Elitco Lighting



Project

Location



PRODUCT DESCRIPTION

producing over 300 lumens, 4.5W ; LED Filament is designed to provide 15,000 hours of life.

SPECIFICATIONS:

- a. Cast aluminum trim with white baffle and flange;
- b. Lamp power: 4.5W;
- c. Power factor ≥ 0.8 ;
- d. 2700K LED color temperature;
- e. 80 CRI minimum; Accommodates 120 volts AC at 60Hz ;
- f. Dimmable with most standard incandescent as dimming list which provided.

INSTALLATION:

connect to city power directly

DIAMETER: 35mm

FINISHES: Clear Cover

LABELS: UL/CUL listed (CUL listed number: E352204) , Energy Star®, FCC Listed, Suitable for damp locations



Model No.	Equivalent	Energy Savings
E12LED101	40W Incandescent	\$59