



SUBMITTAL INFORMATION

70 Series Coppersetter - (VBHH77-xx-41-77-G-NL style)



FLANGED ANGLE BALL VALVE BY FLANGED ANGLE DUAL CHECK VALVE (2" METER)

GRIP JOINT FOR COPPER OR PLASTIC TUBING (CTS) INLET BY FEMALE IRON PIPE THREAD OUTLET



SERVICE LINE CONNECTION		HEIGHT	APPROX. WT. LBS.	CATALOG NUMBER	✓ SUBMITTED ITEM(S)
CTS GJ INLET	FIP OUTLET				
2"	2"	12"	32	VBHH77-12-41-77-G-NL	
		15"	33	VBHH77-15-41-77-G-NL	
		18"	34	VBHH77-18-41-77-G-NL	
		21"	34	VBHH77-21-41-77-G-NL	
		24"	35	VBHH77-24-41-77-G-NL	
		27"	35	VBHH77-27-41-77-G-NL	

Note: Ford recommends using insert stiffeners with plastic pipe or tubing.

FEATURES

- All brass that comes in contact with potable water conforms to AWWA Standard C800 (ASTM B584, UNS C89833)
- The product has the letters "NL" cast into the main body for lead-free identification
- Brass components that do not come in contact with potable water conform to AWWA Standard C800 (ASTM B62 and ASTM B584, UNS C83600, 85-5-5-5)
- Constructed with Type K copper conforms to ASTM B88, UNS C12200
- All Ford Meter Setters are assembled with lead-free solder
- Bracing eyes are standard
- Meter support brackets are standard
- Padlock wing is standard on all angle meter ball valves or key valves
- Dual check valve is ASSE 1024 approved
- Drop-in rubber gaskets are included with all meter flanges
- Optional Bypass on bottom bar - add "B" following the height. Example: VBHH77-12B-41-77-G-NL
- Optional High Bypass - add "HB" following the height. Example: VBHH77-12HB-41-77-G-NL

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.



The Ford Meter Box Company, Inc.
P.O. Box 443, Wabash, Indiana U.S.A. 46992-0443
Phone: 260-563-3171 / Fax: 800-826-3487
Overseas Fax: 260-563-0167
www.fordmeterbox.com

10/04/17

Submitted By: