

DRZ30980RAP
30-INCH FREEZER COLUMN, RIGHT-HINGE
 MODERNIST, PANEL-READY

dacor®



FEATURES & BENEFITS

- Full height door with true flush cabinet integration without exposed venting grille
- SteelCool™ Stainless Steel Interior Illuminated by 3DLighting™
- Push-To-Open™ Door Assist opens the door upon a slight push for a luxuriously convenient experience
- Dual icemaker with Standard and Cocktail Ice™
- Best-in class food preservation with dedicated evaporator/compressor and Precise Cooling Technology

TEMPERATURE RANGES

Freezer	5°F (-15°C) to -8°F (-23°C)
Freezer - Power Freeze	-8°F (-23°C)

ACCESSORIES (OPTIONAL)

Graphite Stainless Steel - 30" Panel (Right Hinge)	RAC30DPRHMS
Graphite Stainless Steel - 30" Kick Plate	RAC30TKBBMS
Graphite Stainless Steel - Modernist Handle	RAC00MHAAMS
Silver Stainless Steel - 30" Panel (Right Hinge)	RAC30DPRHSR
Silver Stainless Steel - 30" Kick Plate	RAC30TKBBSR
Silver Stainless Steel - Modernist Handle	RAC00MHAASR
Silver Stainless Steel - Dacor Pro Handle	RAC00PHAASR
Pair Installation Kit	RAC00CPAAAA
Water Filter	RAC00WFAAAA
Deodorizing Filter	RAC00DFAAAA

GENERAL PROPERTIES

Panel Ready	Yes
Door Swing	Right
Push-To-Open™ Door Assist	Yes
Icemaker	Dual icemaker for Standard and Cocktail Ice™
Lighting	3DLighting™
Interior Material	SteelCool™ Stainless Steel Interior
Full Width Shelves	3 ea
Shelf Material	Tempered, Metal Trim, Spill-Proof
Full Extension Drawers at 90° Door Opening Angle	Yes
Hidden Box with Flip-Up Cover	1 ea
Freezer Drawer	2 ea
Door Bins	4 ea
Door Open Alarm	Yes
Special Modes	Sabbath Mode

CAPACITY

Total Unit Gross Capacity (cu. ft.) - AHAM	17.6 cu. ft.
Freezer Gross Capacity (cu. ft.)	17.6 cu. ft.

PERFORMANCE

Dedicated Evaporator & Compressor System	Yes
Power Freeze	Yes
Defrost Process	Frost-Free
Precise Cooling	Minimized temperature fluctuation ±0.36°F* (±0.2°C*)

EFFICIENCY

ENERGY STAR Qualified	Yes
Annual Energy Consumption	550 kW/year

TECHNICAL DETAILS

Current (A)	6
Volts (V)	115
Frequency (Hz)	60
Power Cord Length (in.)	78 3/4"
Plug Type	120V, 3 Prong

DIMENSIONS & WEIGHT

Appliance dimensions (H x W x D) (in.)	83 3/8" x 29 5/8" x 23 13/16"
Required Cutout Size (H x W x D) (in.)	84" x 30" x 25"
Net Weight (lbs)	483

WARRANTY

Limited, Entire Appliance, Parts and Labor on Any Part of the Refrigerator	2 Year
Limited Warranty for Sealed Refrigeration System; Parts and Labor	3rd to 6th Year
Limited Warranty for Sealed Refrigeration System; Parts Only	7th to 12th Year


DRZ30980RAP

30-INCH REFRIGERATOR COLUMN, RIGHT-HINGE

MODERNIST, PANEL-READY




APPLIANCE DIMENSIONS




	30"
A (Width)	29 5/8" (752mm)
B (Depth)	23 13/16" (605mm)
C (Height)	83 3/8" (2118mm)

INSTALLATION CUTOUT DIMENSIONS



	30"
A (Width)	30" (762mm)
B (Depth)	25" (635mm)
C (Height)	84" (2134mm)
A'	6" (152mm)
B'	20" (508mm)
C'	80" (2032mm)

CUSTOM PANEL DIMENSIONS



	30"
A-1 (Width)	29 3/4" (756mm)
A-2 (Height)	79 7/8" (2029mm)
A-3 (Depth)	3/4" (19mm)
Max Weight	88.0 lbs. (40kg)