

CURB BOXES - EXTENSION TYPE WITH ARCH PATTERN BASE

SLP-27

Extension type curb box with arch pattern base - for 1/2" through 2" curb valves and stops
 Furnished with a cast iron lid and brass pentagon plug. Shut-off rods, foot pieces and pentagon keys are optional equipment and are not furnished with these boxes, but can be ordered separately.

All Mueller boxes are polarized

	A-726	A-728	A-729	A-753	A-714	A-715	A-717
Lid used:	A-800	A-800	A-800	A-806	A-808	A-808	A-808
Telescopes:	12" (300 mm)	12" (300 mm)	12" (300 mm)	9" (225 mm)	24" (600 mm)	24" (600 mm)	24" (600 mm)
Upper section:	1"	1"	1"	2"	1 1/4"	1 1/4"	1 1/4"
Rod diameter	9/16"	3/4"	9/16"	3/4"	9/16"	3/4"	9/16"
Used with:							
Conventional curbs	1/2" thru 1"	1 1/4", 1 1/2", 2"		1 1/2", 2"	1/2" thru 1"	1 1/4", 1 1/2", 2"	
Mark II Oriseal curbs	5/8" thru 1 1/4"	1 1/2", 2"	1 1/2", 2"		5/8" thru 1 1/4"	1 1/2", 2"	1 1/2", 2"

Stainless Steel Rods

Part number includes bronze cotter pin. Add suffix "SS" if stainless steel cotter pin is required


Length	Part No.
29"	88055
35"	88036
45"	88037
56"	88038
71"	88045

Bases for:

A-726, A-728
A-714, A-717

A-728
A-715

A-753



Stationary Rods

Select correct part number to fit appropriate service box

Rod Length	Max. Box Length	A-726 A-729	A-728	A-753	Rod Length	Max. Box Length	A-714 A-717	A-715
17" (45 cm)	2'6" & 3' (75-90 cm)	89002						
23" (60 cm)	3'6" & 4' (105 - 120 cm)	91499	92460	91216				
35" (90 cm)	4'6" & 5' (135 - 155 cm)	89005	92462	91218				
47" (120 cm)	5'5" & 6' (170 - 185 cm)	91814	92464	91220	36" (90 cm)	6' (185 cm)	89005	92462
59" (150 cm)	6'6" & 7' (200 - 215 cm)	89009	92466	91222	47" (120 cm)	7' (215 cm)	91814	92464
71" (180 cm)	7'6" & 8' (230 - 245 cm)	89011	92468	89986	59" (150 cm)	8' (245 cm)	89009	92466
83" (210 cm)	8'6" & 9' (260 - 275 cm)	89013	92470	91320	71" (180 cm)	9' (275 cm)	89011	92468
					83" (210 cm)	10' (305 cm)	89013	92470

Approximate Box Weights including Stationary Rods

Box #	Max. Extn.	A-726	A-728	A-753	A-714	A-715
2	3' (90 cm)	12 lbs. (5.5 kg)	23 lbs. (10.5 kg)	26 lbs. (12.0 kg)		
3	3'6" (105 cm)	14 lbs. (6.5 kg)	25 lbs. (11.5 kg)	28 lbs. (13.0 kg)		
4	4' (120 cm)	15 lbs. (7.0 kg)	26 lbs. (12.0 kg)	31 lbs. (14.0 kg)		
5	4'6" (135 cm)	16 lbs. (7.5 kg)	28 lbs. (13.0 kg)	33 lbs. (15.0 kg)		
6	5' (150 cm)	17 lbs. (8.0 kg)	30 lbs. (13.5 kg)	36 lbs. (16.5 kg)	17 lbs. (8.0 kg)	30 lbs. (13.5 kg)
7	5'6" (170 cm)	19 lbs. (8.5 kg)	31 lbs. (14.0 kg)	38 lbs. (17.0 kg)		
8	6' (185 cm)	20 lbs. (9.0 kg)	33 lbs. (15.0 kg)	41 lbs. (18.5 kg)	20 lbs. (9.0 kg)	33 lbs. (15.0 kg)
9	6'6" (200 cm)	21 lbs. (9.5 kg)	35 lbs. (16.0 kg)	43 lbs. (19.5 kg)		
10	7' (215 cm)	23 lbs. (10.5 kg)	36 lbs. (16.5 kg)	46 lbs. (21.0 kg)	23 lbs. (10.5 kg)	36 lbs. (16.5 kg)
11	7'6" (230 cm)	24 lbs. (11.0 kg)	38 lbs. (17.0 kg)	49 lbs. (22.0 kg)		
12	8' (245 cm)	25 lbs. (11.5 kg)	39 lbs. (17.5 kg)	51 lbs. (23.0 kg)	25 lbs. (11.5 kg)	39 lbs. (17.5 kg)
14	9' (275 cm)	28 lbs. (13.0 kg)	43 lbs. (19.5 kg)	56 lbs. (25.5 kg)	28 lbs. (13.0 kg)	43 lbs. (19.5 kg)
16	10' (305 cm)	31 lbs. (14.0 kg)	46 lbs. (21.0 kg)	61 lbs. (28.0 kg)	31 lbs. (14.0 kg)	46 lbs. (21.0 kg)

For A-729 box weight add 6 lbs. (2.7 kg) to A-726 weight/For A-717 box weight add 6 lbs. (2.7 kg) to A-714 weight.
 Order boxes by quantity, extended length and catalogue number, stationary rods by quantity and part number.



A-726/A-714