

## Light and mirror Mirror with lighting # LM7826D0000

|< 31 1/2" Inch >|



Mirror with lighting	Dimension	Weight	Order number
Premium-Version, cEGS/IAPMO®, LED ambient light (4 sided), LED dimming function, 1 sensor switch bottom right, de-fogging system with Auto-Off function, mirrors require a GFCI 110 V 60 Hz power source, flat plug will be supplied with mirror, LED (life span > 30,000 hours), LED module permanently enclosed, LED module 4000 kelvin light color, 42 Watt			
<b>Colors</b>			
00 White			
<b>Variant</b>			
	31 1/2" x 1 1/4" Inch		LM7826D0000
<b>Infobox</b>			
# LM 7825, LM 7826, LM 7827 and LM 7828 are available from stock, Distance between sensor and reflecting surfaces = minimum 3", Sensor controls both light and heater, * Complies with following standards: UL 962 and CSA C22.2 No. 12-1982			

*All drawings contain the necessary measurements which are subject to standard tolerances. They are stated in inch & mm and are non-binding. Exact measurements, in particular for customized installation scenarios, can only be taken from the finished ceramic piece.*