

## L-Cube Mirror with lighting # LC738500000

|< 63" Inch >|



Mirror with lighting	Dimension	Weight	Order number
cEGS/IAPMO®, LED lighting (4-sided), LED dimming function, 1 sensor switch bottom right, mirrors require a GFCI 110 V 60 Hz power source, flat plug will be supplied with mirror, LED (life span > 30,000 hours), LED module permanently enclosed, LED module 3500 kelvin light color, 67 Watt			
<b>Colors</b>			
M00			
<b>Variant</b>			
	63" x 2 5/8" Inch		LC738500000
<b>Infobox</b>			
# LC 7379 - LC 7385 and LC 7388 are available from stock, Distance between sensor and reflecting surfaces = minimum 3", * Complies with following standards: UL 962 and CSA C22.2 No. 12-1982			
Additional modules de-fogging system with Auto-Off function, mirror widths 51 1/8", 52", 55 1/8", 55 7/8", 63", 63 3/4" 74 Watt			UV9774

*All drawings contain the necessary measurements which are subject to standard tolerances. They are stated in inch & mm and are non-binding. Exact measurements, in particular for customized installation scenarios, can only be taken from the finished ceramic piece.*