


## Light and mirror Mirror with lighting # LM7866

|< 31 1/2" Inch >|



Mirror with lighting	Dimension	Weight	Order number
Standard-Version, cEGS/IAPMO®, LED dual light fields, external switch, mirrors require a GFCI 110 V 60 Hz power source, flat plug will be supplied with mirror, LED (life span > 30,000 hours), LED module permanently enclosed, LED module 4000 kelvin light color, 20 Watt			
Colors			
Variant			
	31 1/2" x 1 3/8" Inch		LM7866
Infobox			
# LM 7865, LM 7866, LM 7867 and LM 7868 are available from stock, On/off function only possible with external wall switch, * Complies with following standards: UL 962 and CSA C22.2 No. 12-1982			

All drawings contain the necessary measurements which are subject to standard tolerances. They are stated in inch & mm and are non-binding. Exact measurements, in particular for customized installation scenarios, can only be taken from the finished ceramic piece.