


[Home](#) > [Blue White](#) > [Blue White](#) > [Pumps](#) > [Peristaltic Pumps](#) > [Metering Pumps](#) > [A1N30V-2T-P](#)

Blue White A1N30V-2T-P Peristaltic Metering Pump

Item#: A1N30V-2T-P | **Model#:** A1N30V-2T-P **Series#:** A1NXXV-XX-P

Description:

Blue White A1N30V-2T-P Flex-Flo A-100N Peristaltic Metering Pump. Tubing Connection Type Compression tube nuts, Output Control Digital speed control with external input

 Price: **USD \$1252⁸⁹**
[Buy Now](#)

Technical Specification

A1N30V-2T-P Product Specific Data

Maximum Motor RPM	60 RPM
Power Supply	115V/60 Hz
Output Control	Digital speed control with external input
Pump Tube Size and Material	3/8" OD Flex-A-Thane
Tubing Connection Type	Compression tube nuts

Series Data

Type	Peristaltic Metering
Max Feed	3.96 gph (15 lph)
Max Pressure	100 psi (6.9 bar)
Max Temperature	130° F (54° C)
Max Ambient Temperature	14° to 110° (-10° to 43° C)
Duty Cycle	Continuous
Max Viscosity	5,000 Centipoise
Max Suction Lift	30 ft. Water 0 psig
Max Solid	50% by volume
Enclosure	NEMA 3R, (IP23)

Product Dimensions

Weight	0.00 lb
Width	241.00 mm, 9.49 in
Height	232.00 mm, 9.13 in
Length	152.00 mm, 5.98 in

Technical Documents

Document Title	Download
Instruction Manual	Click Here to Download
Technical Datasheet	Click Here to Download
Exploded View	Click Here to Download

Parts List

Position	Part Number	Part Details	Quantity	Price
14	71000-188	71000-188 - Encl, Fixed model " " - P/Cord for Metering Pumps by Blue White	1	\$104.83
17	70002-159	70002-159 - Gearmotor for Metering Pumps by Blue White	1	\$395.86
50	90006-601	90006-601 - Motor Clip for Metering Pumps by Blue White	1	\$6.57