





With Western the water savings are significant and maintenance is minimal.

Our customers tell us it's "The Best Flushing Toilet in America!"

- Round front bowl.
- Up to 20% water savings over conventional 1.6 gpf toilets.
- J Sani-Glazed™ trapway gives years of sanitary, trouble free use.
- Powerful Vortex-Jet<sup>™</sup> flushing system scrubs the bowl with every flush.
- Full size water surface and seal for a clean and sanitary bowl.
- Quick-Install™ tank to bowl fittings speed installation and helps reduce potential leaks.
- Front mount color-matched handle.
- Also available with 10" & 14" rough-in.
- Available in Western White and Cashmere.
- Seat not included.
- All Western products are IAPMO tested and meet or exceed standards.
- Certified by IAPMO to meet or exceed the EPA WaterSense standards.

For more information please contact us toll-free:

877-WPWORKS (979-6757)

**US Sales and Service** 

Phone 562.229.0910 • Fax 562.229.0930

www.westernpottery.com • Email: info@westernpottery.com

14405 Best Avenue • Norwalk, California 90650

# B822 / T8-HET 1.28 gpf / 4.8 Lpf

#### **PHYSICAL PROPERTIES**

Model: B822 / T8-HET

Water Surface: 6-7/8" x 8-1/16"

(172mm x 205mm)

Trapway: 2" (50mm)

Water Consumption: 1.28 gpf (4.80 Lpf)

Shipping Weight: 50 lbs bowl


33 lbs tank

Shipping Cube: 3.86 ft bowl

1.62 ft tank

Rough-in: 12" (305mm)

MaP Rating: 800 grams



change without notice.



# B822 / T8-HET-RH 1.28 gpf / 4.8 Lpf

#### **PHYSICAL PROPERTIES**

Model: B822 / T8-HET-RH

Water Surface: 6-7/8" x 8-1/16"

(172mm x 205mm)

Trapway: 2" (50mm)

Water Consumption: 1.28 gpf (4.80 Lpf)

Shipping Weight: 50 lbs bowl


33 lbs tank

Shipping Cube: 3.86 ft bowl

1.62 ft tank

Rough-in: 12" (305mm)

MaP Rating: 800 grams



change without notice.



### B822 / T8ULF HET-10 1.28 gpf

#### **PHYSICAL PROPERTIES**

Model: B822 / T8-HET-10

Water Surface: 6-7/8" x 8-1/16"

(172mm x 205mm)

Trapway: 2" (50mm)

Water Consumption: 1.28 gpf (4.80 Lpf)

Shipping Weight: 50 lbs bowl


33 lbs tank


Shipping Cube: 3.86 ft bowl

1.54 ft tank

Rough-in: 10" (254mm)

MaP Rating: 800 grams







### B822 / T8 HET-10-RH 1.28 gpf

#### **PHYSICAL PROPERTIES**

Model: B822 / T8-HET-10-RH

Water Surface: 6-7/8" x 8-1/16"

(172mm x 205mm)

Trapway: 2" (50mm)

Water Consumption: 1.28 gpf (4.80 Lpf)

Shipping Weight: 50 lbs bowl


33 lbs tank

Shipping Cube: 3.86 ft bowl

1.54 ft tank

Rough-in: 10" (254mm)

MaP Rating: 800 grams





## B822/T8 HET-14 1.28 gpf

#### **PHYSICAL PROPERTIES**

Model: B822 / T8-HET-RH-14

Water Surface: 6-7/8" x 8-1/16"

(172mm x 205mm)

Trapway: 2" (50mm)

Water Consumption: 1.28 gpf (4.80 Lpf)

Shipping Weight: 50 lbs bowl


40 lbs tank

Shipping Cube: 3.86 ft bowl

2.00 ft tank

Rough-in: 14" (356mm)

MaP Rating: 800 grams



change without notice.

