



Category 22

Commercial Drainage

Oatey® commercial drains are designed to stand up to heavy traffic areas. Preformed anchor positions are included in each base design and drain barrels include internal thread that accepts clean-out plugs. Four grate finishes are available: Stainless Steel, Nickel, Chrome and Brass.

**COMPLETE DRAIN,
COMPLETE LINE,
COMPLETE SOLUTION.**
*Easy leveling drain for
a “True Set” every time.* (see page 204)

The Oatey® True Set™ adjustable drain uses an easy-leveling strainer mount to correct tilted drains! This unique, patent pending design quickly solves the problem of drain installs knocked out of plumb after the concrete is poured.

That along with the highest post-pour height adjustment in the industry means the Oatey True Set adjustable drain gives you a level installation to the finished floor every time! See pages 202-205 for a complete product list.

- **Complete Versatility**
 - Ready for use right out of the box
 - Provides a level installation to the finished floor every time
 - Concrete tight protection
 - Interchangeable drain and cleanout
 - Multiple sizes, materials and finishes available
- **Complete Confidence / Post Pour Leveling**
 - Largest adjustment range in the industry
 - Height and pitch adjustments
- **Complete Assembly**
 - No spare parts to lose
- **Complete Safety / Load Capacity**
 - C-UPC listed and medium duty IAPMO rated



Part Number Legend (Example: TP211S)

T	P	2	1	1	S
T- True-Set	P- PVC	2- 2" Outside/3" Inside Solvent	1- Flanged Drain	1- 5" Round	S- Stainless Steel
	A- ABS	3- 3" Outside/4" Inside Solvent	2- Flanged CO	2- 5" Round w/ Ring	B- Brass
		4- 4" Outside Solvent	3- GP Drain	3- 6" Round	N- Nickel Bronze
			4- GP CO	4- 6" Round w/ Ring	C- Chrome
			5- SS Flanged Drain	5- 5" Square w/ Ring	
			6- SS Flanged CO	6- 6" Square w/ Ring	



			Stamped SS Strainer Round	Die Cast Brass Strainer			Die Cast Nickel Strainer			Die Cast Chome Plated Strainer		
				Round	Round w/Ring	Square w/Ring	Round	Round w/Ring	Square w/Ring	Round	Round w/Ring	Square w/Ring
5" Strainer	PVC On-Grade Base	Over 2" / Inside 3" Pipe Fit	TP231S ⁺	TP231B	TP232B	TP235B	TP231N	TP232N	TP235N	TP231C	TP232C	TP235C
		Over 3" / Inside 4" Pipe Fit	TP331S ⁺	TP331B*	TP332B*	TP335B	TP331N*	TP332N*	TP335N	TP331C*	TP332C*	TP335C
		Over 4" Pipe Fit	TP431S ⁺	TP431B*	TP432B*	TP435B*	TP431N*	TP432N*	TP435N*	TP431C*	TP432C*	TP435C*
	ABS On-Grade Base	Over 2" / Inside 3" Pipe Fit	TA231S ⁺	TA231B	TA232B	TA235B	TA231N	TA232N	TA235N	TA231C	TA232C	TA235C
		Over 3" / Inside 4" Pipe Fit	TA331S ⁺	TA331B*	TA332B*	TA335B	TA331N*	TA332N*	TA335N	TA331C*	TA332C*	TA335C
		Over 4" Pipe Fit	TA431S ⁺	TA431B*	TA432B*	TA435B*	TA431N*	TA432N*	TA435N*	TA431C*	TA432C*	TA435C*
	PVC Flange Base	Over 2" / Inside 3" Pipe Fit	TP211S ⁺	TP211B	TP212B	TP215B	TP211N	TP212N	TP215N	TP211C	TP212C	TP215C
		Over 3" / Inside 4" Pipe Fit	TP311S ⁺	TP311B*	TP312B*	TP315B	TP311N*	TP312N*	TP315N	TP311C*	TP312C*	TP315C
		Over 4" Pipe Fit	TP411S ⁺	TP411B*	TP412B*	TP415B*	TP411N*	TP412N*	TP415N*	TP411C*	TP412C*	TP415C*
	ABS Flange Base	Over 2" / Inside 3" Pipe Fit	TA211S ⁺	TA211B	TA212B	TA215B	TA211N	TA212N	TA215N	TA211C	TA212C	TA215C
		Over 3" / Inside 4" Pipe Fit	TA311S ⁺	TA311B	TA312B*	TA315B	TA311N*	TA312N*	TA315N	TA311C*	TA312C*	TA315C
		Over 4" Pipe Fit	TA411S ⁺	TA411B*	TA412B*	TA415B*	TA411N*	TA412N*	TA415N*	TA411C*	TA412C*	TA415C*
6" Strainer	PVC On-Grade Base	Over 2" / Inside 3" Pipe Fit	TP233S ⁺	TP233B	TP234B	TP236B	TP233N	TP234N	TP236N	TP233C	TP234C	TP236C
		Over 3" / Inside 4" Pipe Fit	TP333S ⁺	TP333B	TP334B	TP336B	TP333N	TP334N	TP336N	TP333C	TP334C	TP336C
		Over 4" Pipe Fit	TP433S ⁺	TP433B*	TP434B*	TP436B*	TP433N*	TP434N*	TP436N*	TP433C*	TP434C*	TP436C
	ABS On-Grade Base	Over 2" / Inside 3" Pipe Fit	TA233S ⁺	TA233B	TA234B	TA236B	TA233N	TA234N	TA236N	TA233C	TA234C	TA236C
		Over 3" / Inside 4" Pipe Fit	TA333S ⁺	TA333B	TA334B	TA336B	TA333N	TA334N	TA336N	TA333C	TA334C	TA336C
		Over 4" Pipe Fit	TA433S ⁺	TA433B*	TA434B*	TA436B	TA433N*	TA434N*	TA436N	TA433C*	TA434C*	TA436C
	PVC Flange Base	Over 2" / Inside 3" Pipe Fit	TP213S ⁺	TP213B	TP214B	TP216B	TP213N	TP214N	TP216N	TP213C	TP214C	TP216C
		Over 3" / Inside 4" Pipe Fit	TP313S ⁺	TP313B	TP314B	TP316B	TP313N	TP314N	TP316N	TP313C	TP314C	TP316C
		Over 4" Pipe Fit	TP413S ⁺	TP413B*	TP414B*	TP416B	TP413N*	TP414N*	TP416N	TP413C*	TP414C*	TP416C
	ABS Flange Base	Over 2" / Inside 3" Pipe Fit	TA213S ⁺	TA213B	TA214B	TA216B	TA213N	TA214N	TA216N	TA213C	TA214C	TA216C
		Over 3" / Inside 4" Pipe Fit	TA313S ⁺	TA313B	TA314B	TA316B	TA313N	TA314N	TA316N	TA313C	TA314C	TA316C
		Over 4" Pipe Fit	TA413S ⁺	TA413B*	TA414B*	TA416B	TA413N*	TA414N*	TA416N	TA413C*	TA414C*	TA416C

(*) indicates drain only conforms to CSA B79.

(+) indicates stamped stainless steel strainer, does not meet C-UPC and is light duty rated.

All non-stainless steel strainers are medium duty rated for 2000 lbs. minimum.

All drain part numbers not marked with (*) or (+) meet ASME A112.6.3 and CSA B79 commercial drain standards.

Part Number Legend (Example: TP211S)

T	P	2	1	1	S
T- True-Set	P- PVC	2- 2" Outside/3" Inside Solvent	1- Flanged Drain	1- 5" Round	S- Stainless Steel
	A- ABS	3- 3" Outside/4" Inside Solvent	2- Flanged CO	2- 5" Round w/ Ring	B- Brass
		4- 4" Outside Solvent	3- GP Drain	3- 6" Round	N- Nickel Bronze
			4- GP CO	4- 6" Round w/ Ring	C- Chrome
			5- SS Flanged Drain	5- 5" Square w/ Ring	
			6- SS Flanged CO	6- 6" Square w/ Ring	



			Stamped SS Strainer Round	Die Cast Brass Strainer			Die Cast Nickel Strainer			Die Cast Chome Plated Strainer		
				Round	Round w/ Ring	Square w/ Ring	Round	Round w/ Ring	Square w/ Ring	Round	Round w/ Ring	Square w/ Ring
5" Clean-out	PVC On-Grade Base	Over 2" / Inside 3" Pipe Fit	N/A	TP241B	TP242B	N/A	TP241N	TP242N	N/A	TP241C	TP242C	N/A
		Over 3" / Inside 4" Pipe Fit	N/A	TP341B	TP342B	N/A	TP341N	TP342N	N/A	TP341C	TP342C	N/A
		Over 4" Pipe Fit	N/A	TP441B	TP442B	N/A	TP441N	TP442N	N/A	TP441C	TP442C	N/A
	ABS On-Grade Base	Over 2" / Inside 3" Pipe Fit	N/A	TA241B	TA242B	N/A	TA241N	TA242N	N/A	TA241C	TA242C	N/A
		Over 3" / Inside 4" Pipe Fit	N/A	TA341B	TA342B	N/A	TA341N	TA342N	N/A	TA341C	TA342C	N/A
		Over 4" Pipe Fit	N/A	TA441B	TA442B	N/A	TA441N	TA442N	N/A	TA441C	TA442C	N/A
	PVC Flange Base	Over 2" / Inside 3" Pipe Fit	N/A	TP221B	TP222B	N/A	TP221N	TP222N	N/A	TP221C	TP222C	N/A
		Over 3" / Inside 4" Pipe Fit	N/A	TP321B	TP322B	N/A	TP321N	TP322N	N/A	TP321C	TP322C	N/A
		Over 4" Pipe Fit	N/A	TP421B	TP422B	N/A	TP421N	TP422N	N/A	TP421C	TP422C	N/A
	ABS Flange Base	Over 2" / Inside 3" Pipe Fit	N/A	TA221B	TA222B	N/A	TA221N	TA222N	N/A	TA221C	TA222C	N/A
		Over 3" / Inside 4" Pipe Fit	N/A	TA321B	TA322B	N/A	TA321N	TA322N	N/A	TA321C	TA322C	N/A
		Over 4" Pipe Fit	N/A	TA421B	TA422B	N/A	TA421N	TA422N	N/A	TA421C	TA422C	N/A
6" Clean-out	PVC On-Grade Base	Over 2" / Inside 3" Pipe Fit	N/A	TP243B	TP244B	N/A	TP243N	TP244N	N/A	TP243C	TP244C	N/A
		Over 3" / Inside 4" Pipe Fit	N/A	TP343B	TP344B	N/A	TP343N	TP344N	N/A	TP343C	TP344C	N/A
		Over 4" Pipe Fit	N/A	TP443B	TP444B	N/A	TP443N	TP444N	N/A	TP443C	TP444C	N/A
	ABS On-Grade Base	Over 2" / Inside 3" Pipe Fit	N/A	TA243B	TA244B	N/A	TA243N	TA244N	N/A	TA243C	TA244C	N/A
		Over 3" / Inside 4" Pipe Fit	N/A	TA343B	TA344B	N/A	TA343N	TA344N	N/A	TA343C	TA344C	N/A
		Over 4" Pipe Fit	N/A	TA443B	TA444B	N/A	TA443N	TA444N	N/A	TA443C	TA444C	N/A
	PVC Flange Base	Over 2" / Inside 3" Pipe Fit	N/A	TP223B	TP224B	N/A	TP223N	TP224N	N/A	TP223C	TP224C	N/A
		Over 3" / Inside 4" Pipe Fit	N/A	TP323B	TP324B	N/A	TP323N	TP324N	N/A	TP323C	TP324C	N/A
		Over 4" Pipe Fit	N/A	TP423B	TP424B	N/A	TP423N	TP424N	N/A	TP423C	TP424C	N/A
	ABS Flange Base	Over 2" / Inside 3" Pipe Fit	N/A	TA223B	TA224B	N/A	TA223N	TA224N	N/A	TA223C	TA224C	N/A
		Over 3" / Inside 4" Pipe Fit	N/A	TA323B	TA324B	N/A	TA323N	TA324N	N/A	TA323C	TA324C	N/A
		Over 4" Pipe Fit	N/A	TA423B	TA424B	N/A	TA423N	TA424N	N/A	TA423C	TA424C	N/A

All Cleanouts meet both ASME A112.6.3 & CSA B79 standards.

Note: Strainers and Covers are medium duty load rated.

SS - Stainless Steel BR - Brass NI - Nickel CHR - Chrome