# TruAct BV88 2", 3" & 4" Digital Control Valve



The Model BV 88 Digital Control Valve is designed to provide precise flow rate control and batch delivery of fluid products when used with an electronic batch control device. The Model BV88 features an external pilot control loop that consisits of a normally - open solenoid pilot, a normally - closed solenoid pilot, strainer, and opening/closing speed controls.

### **DESIGN FEATURES**

- Precision flow rate and batch control
- Modular construction all internal parts including seat ring can be removed with the cylinder assembly without disturbing line connections
- No diaphragms or stuffing boxes
- 45° Body design assures high capacity
- Positive Shut off
- Linear control characteristics with uniform response speed
- Automatic check valve no reverse flow
- Fail-Safe, closes on loss of electric power
- Characterized ports for better low flow response



# TruAct BV88 2", 3" & 4" Digital Control Valve

#### **VALVE CAPACITY DATA**

Valve Size	2"	3"	4"	
*Cv-gpm	90	190	315	
*Cv based on wide open valve utilizing water at 60F (15.6C).				

#### **CONSTRUCTION MATERIALS:**

Main Valve Body: Steel - ASTM - A216 - GR - WCB Main Valve Cylinder: 17-4 Stainless Steel, Heat Treated

Main Valve Piston: Stainless Steel

Seat Ring: Stainless Steel

O-Rings: Viton Standard (Other elastomers available)

Other Internal Parts: Stainless Steel

Pilot Valve Strainer / Needle Valve Stainer: Steel (standard)

Tubing & Fittings: Steel (standard)

## Maximum Operating Pressure Differential (M.O.P.D.) Across Pilots

150 lb. Standard 100 psid 690 kPa Optional 150 psid 1,035 kPa Optional 285 psid 1,967 kPa 300 lb. Standard 740 psid 5106 kPa

#### **FLANGE CONNECTIONS**


Valve Size	Connections	Max Working Pressure @100F
2" - 4"	150 lb. ANSI	285 PSI
2" - 4"	300 lb. ANSI	740 PSI

## **DIMENSIONS**(For Certified Dimensional Prints - Consult Factory)

Valve	mm	A Dimensions		B Dimensions
Size	inches	150 lb	300 lb	150 & 300 lb
2"	mm	260	267	280
	inches	10-1/4	10-1/2	11
3"	mm	279	333	286
	inches	11	13-1/8	11-1/4
4"	mm	330	368	292
	inches	13	14-1/2	11-1/2

### **SHIPPING WEIGHT & VOLUME (Approximate)**

Valve Size		
2"	69 lbs. @ 3 Cu. Feet 31.3 kgs. @ .085 Cu. Meters	
3"	105 lbs. @ 2.36 Cu. Feet 47.63 kgs. @ .067 Cu. Meters	
4"	140 lbs. @ 2.51 Cu. Feet 63.5 kgs. @ .071 Cu. Meters	







Brodie Meter, Co. LLC

19267 Highway 301 North • Statesboro, GA 30461 USA Phone: 001-912-489-0200 www.brodie-savmor.com