

Item #: **P5046-084-L**
 Product Family Name:
 Category: **Bath**
 Certification: **4006873**
 Patents
 Notes:

UPC Code: **844349013105**
 Finish: **Brushed Nickel**
 Category Type: **Bath**



Mounted Horizontally or Vertically

Image File Name:
 P5046-084-L--
 1377187721.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
39.75		4.75	4.5
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
7		No	6.35
Canopy Width:	Canopy Height:	Canopy Length:	
6.50	4.75		
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:
		2.38	2.38

LAMPING

No. of Bulbs:	Light Type:			
2	L-L22-Module			
Max Bulb Wattage:	Socket:			
40	Led			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
Yes		30000	N	Yes
LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
Yes	3000	98	3110.000	2260.000



SHIPPING

Carton Width:	Carton Height:	Carton Length:
7.750	6.125	42.500
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
7.920	1.167	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		1
		Master Pack:
		1

SHADE / GLASS

Description:	Material:
	Glass
Part No.:	Quantity:
PG5044	2
Width:	Height:
2.38	
	Length:
	18.75

LED

LED

Yes



Title 17

Yes



ETL Intertek

Yes