

XSquare Mirror with lighting # XS7012

|< 31 1/2" Inch >|



| Mirror with lighting | Dimension | Weight | Order number |
|--|-----------------------|--------|--------------|
| cEGS/IAPMO®*, LED dual light fields, 24 Watt, LED ambient light (top & bottom 15-45 Watt), LED dimming function, de-fogging system with Auto-Off function, progressive, synchronous adjustment of the light color for direct and ambient light, dimming function and adjustment of the light color with memory effect, touchless control panel, LED (life span > 30,000 hours), LED module permanently enclosed, mirrors require a GFCI 110 V 60 Hz power source, flat plug will be supplied with mirror, LED module 2700 - 6500 kelvin light color, 45 Watt | | | |
| Colors | | | |
| | | | |
| Variant | | | |
| | 31 1/2" x 1 3/8" Inch | | XS7012 |
| Infobox | | | |
| # XS 7011 and XS 7012 are available from stock, On/off function only possible with external wall switch, * Complies with following standards: UL 962 and CSA C22.2 No. 12-1982 | | | |
| | | | |

All drawings contain the necessary measurements which are subject to standard tolerances. They are stated in inch & mm and are non-binding. Exact measurements, in particular for customized installation scenarios, can only be taken from the finished ceramic piece.