


STC-xx and STCU-xx Signatouch Series Control





SPECIFICATIONS – Signature Control

Construction	Black Acrylic or 6061 Aluminum
Display	5" Capacitive Touch screen
Display Full Color	r16.7N
Display resolution	n480 x 80
Interface	Single Touch

Signatouch Series operational features:

- Digital Shower
 - Operates flow, temperature, and output
- Steam Shower
 - Operates time, temperature, and auto powerflush
- · Light Sound and rainhead
 - Control linked Bluetooth device
 - Control moodlight, shower light, and chromatherapy.

Signatouch Series features:

- Can be mounted vertically or horizontally
- 2 user settings
- Day clock
- 16 finishes

Installation Notes:

The control should be installed 60" inches from the floor of the shower, inside the shower only, and away from the steam head.

Product Specification:

The user interface control shall be 5.6" x 3.5" x 0.65" in dimension. The Control shall be made from black acrylic(-BK,-WHT) or billet aluminum (Other Finishes) and includes the ability to operate and control: Smart Steam, Fast Start, Auto PowerFlush, Light and Sound System. By using a 100% networked digital technology.

Finish Chart:

If selecting "WHT" or "BK" finish replace -xx with code in part number STC-xx. All other finishes replace the -xx in part number STCU-xx.

PC = Polished Chrome SC = Satin Chrome

PB = Polished Brass SB = Satin Brass AB = Antique Brass


COP = Polished Copper ACOP = Antique Copper MB = Matte Black PN = Polished Nickel SN = Satin Nickel BN = Black Nickel AN = Antique Nickel


PG = Polished Gold ORB = Oil Rubbed Bronze

WHT = White BK = Black

Shipping Information:

Weight..........1.25 lbs. Length......9.5 in. Width......6.5 in. Height.....2.5 in. 1.25"





For any further assistance please contact ThermaSol at 800.776.0711 or sales@thermasol.com

Visit www.thermasol.com for a complete product definition









SPECIFICATIONS - SteamVection Steam Head

Construction...... Brass
Aromatherapy...... Integral Reservoir

Installation Notes:

The steam head should be installed 24 inches from the floor, and 6 inches from any corner, inside the shower only, and as far away from the controller and shower fixtures as possible.

The steam head housing requires a 1-1/8" hole in the shower wall, and must be flush with the finished wall and sealed to the wall to not allow vapor or water behind it. Use ½" copper fittings to attach the housing to the steam outlet. See the full steam head housing instructions within your generator installation guide.

Product Specification:

The steam head shall be approximately 1.75" x 1.75" in the square version, and a 1.75" Dia. For the round version. The steam head is made from brass alloy and includes an aromatherapy well.

Shipping Information:

 For any further assistance please contact
ThermaSol at 800.776.0711 or
sales@thermasol.com

Finish Chart:

Select desired finish and replace XX with code. No-Touch Aromatherapy steam head and control finishes.

PC = Polished Chrome

SC = Satin Chrome

PB = Polished Brass

SB = Satin Brass

AB = Antique Brass

COP = Polished Copper

ACOP = Antique Copper

MB = Matte Black

PN = Polished Nickel

SN = Satin Nickel BN = Black Nickel

AN = Antique Nickel

PG = Polished Gold

ORB = Oil Rubbed Bronze

WHT = White

