

UNIVERSAL PIPE HANGER

553-0 series

ZipStick™

Item # Submitted	_____
Job Name	_____
Location	_____
Engineer	_____
Contractor	_____
PO#	_____ TAG _____

SPECIFICATION

Sioux Chief ZipStick Universal Pipe Hanger shall be used where necessary to support DWV piping according to all national code requirements. Hanger shall be noncorrosive and UV-resistant. Hanger shall be impact resistant to 0°F, and be able to withstand temperatures up to 140°F. Hanger shall be marked with manufacturer's name. Product shall be tested and certified to IAPMO product standard PS-9501.

Hanger shall have two pre-loaded zinc plated, rust resistant nails. Nails shall have a continuous rink shank to provide a more permanent installation. Hanger shall feature I-beam stem design for strength and rigidity and a high heat strap with a releasable locking mechanism. Hanger stem may be snapped off or cut to create a shorter hanger for tight spaces. Hanger stem may be extended buy using optional stainless steel L-bracket and all-thread rod with approved hardware. L-bracket shall be secured to hanger stem using two #8 screws (provided).

Hanger may be used to support wrapped or insulated pipe, bundles of flexible tube, cabling or wire or supporting vent pipe in attics. Universal strap can support 1" CTS to 6" IPS. Additional straps may be used to extend the strap length to hang flexible ducting or similar objects of larger diameter, which do not exceed the load ratings listed on this specification.

MATERIALS

- stem: ABS, U.V. resistant, corrosion-proof, impact-resistant
- strap: high-heat polypropylene
- nail: 1⁵/₈" rust-resistant, zinc-plated, continuous rink shank
- I-bracket: 14-gauge, stainless steel
- screw: #8 × 1" zinc-plated hex

INSTALLATION

Nail stem of hanger to joist or stud location using ring shank nails (provided). Position strap around pipe then insert strap into square locking mechanism then pull down on strap until strap cinches tightly around pipe. Excess strap may be cut if desired.

SAFE WORKING LOADS



- 50 lbs @ 32°F
- 50 lbs @ 72°F
- 25 lbs @ 140°F (140°F is maximum safe working temperature)

CERTIFICATIONS

UPC IAPMO, File #3540

DIMENSIONS

	-010	-014	-026
A: ZipStick length	10.0"	14.0"	26.0"
B: ZipStick width	0.875"	0.875"	0.875"
C: ZipStrap width	0.75"	0.75"	0.75"
D: Nailway spacing	1.0"	1.0"	1.0"



Create Item Number

553-0 A B

e.g. 553-026W = 26" white ZipStick universal pipe hanger

- A** LENGTH
 - 10 10" long
 - 14 14" long
 - 26 26" long
 - L ZipStrap strap only

- B** COLOR
 - B black
 - W white

- ACCESSORIES**
 - 521-210 L-Bracket