




Incandescent-Halogen

**4" Low Voltage (MR 16)
Slotted Trim
IC & Non-IC**

Recessed

Type _____
-28
P8039

Catalog No.	Finish White	Dimensions (Inches)	
		A	Slot Size
P8039	-28	5	1/4 x 2-1/4



Lamp Wattage Housing	IC	Non-IC
P817-AT	35MR16	50MR16
P816-TG	N/A	50MR16
P818-TG	N/A	50MR16

Specifications:

Flange

- Bright white powder painted metal flange
- No light leaks around trim flange
- Covers irregular ceiling openings

Labels

- UL-CUL damp location listed

Photometrics

- Refer to MR16 Lamp Application Data

Trim

- Push-in leaf spring action for trim retention forces trim to fit snugly against the ceiling
- Lamp tilt 30 degrees, 360 degrees positioning
- Internal black baffle
- Slot size - 1-1/4" wide, 2-1/4" long

Progress Lighting
701 Millennium Blvd.
Greenville, South Carolina
29607

www.progresslighting.com