

Project:	
Fixture Type:	
Location:	
Contact:	

Semi-Flush/Convertible

Ceiling/Chain mounted • Damp location listed PROGRESS LED



Description:

Designed for both commercial and residential interiors, Apogee is an energy efficient, high performance LED fixture. All fixtures feature 120-277V input with standard dimming. Etched glass shade provides an even and pleasing light effect. Apogee is 3000K, 90+ CRI and meets California Title 24 -JA8 - 2016 standards and is ENERGY STAR rated and damp location listed. The Apogee Collection 27" LED Semi-Flush/Convertible is complimented by a Brushed Nickel finish.

Specifications:

- Brushed Nickel (-009) (plated)
- Steel Construction
- Etched Glass shade
- Semi-flush fixture convertible to hanging pendant with included hardware and instructions.
- Commercial-grade construction and performance.
- · Features Brushed Nickel finish.
- · Etched glass shade provides an even and pleasing light effect.
- · Features 62.7-watt integrated LED to deliver energy savings and reduce long-term maintenance
- · 120-277V operation, 0-10V compatible dimming.
- · 3000K color temperature, 90CRI.
- · 4215 lm, 67.1 Lum/Watt.
- · Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 15 feet of wire supplied
- Six feet of 9 gauge chain supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	62.7w
Input Voltage	120-277 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	4215/67.1 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	58,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class A
Min. Start Temp	-30 °C
Max. Operating Temp	30°C
Warranty	5 year limited warranty
Labels	cETLus Damp location listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016

P350066-009-30

Images:



Dimensions:

Diameter: 27" Height: 20-5/8"

Overall Ht. W/Chain: 98"

Glass

Width: 24-1/2" Height: 3-7/8"



Semi-Flush/Convertible





P350066-009-30

Dimming Notes:

P350066 is designed to be compatible with many 0-10V controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron - NFTV

Lutron - NTFTV

Lutron - DVTV

Leviton - AWSMT-7DW

Leviton - IP710

Lithonia ISD BC

Pass & Seymour - CD4FB

Wattstopper ADF-120277

Hunt Dimming - PS-010-120V

Hunt Dimming - PS010 277V

Lightolier Controls - MP1500FAM120

Lightolier Controls - ZP600FAM120

Synergy Lighting Controls - V2000FAMU

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.