

Two-Light Ceiling Fan Light Kit

• Dry location listed **PROGRESS LED** 

Description:

Alabaster style glass bowl ceiling fan light kit casts an inviting illumination in any size room. Includes (-09) Brushed Nickel, (-15) Polished Chrome, (-20) Antique Bronze, (-30) white, and (-143) Graphite finials for use with matching Progress Lighting fans. Universal style lets you use with any indoor fan that accept an accessory light. Quick-connect wiring makes the installation process quick and easy. Includes two 3000K, 800 lumen each (source), Title 24 certified LED bulbs.

Specifications:

- Unfinished (-01)
- Steel Construction
- Alabaster glass Bowl
- Elegant alabaster glass bowl casts an inviting illumination.
- Includes (-09) Brushed Nickel, (-15) Polished Chrome, (-20) Antique Bronze, (-30) white, and (-143) Graphite finials for use with matching Progress Lighting fans.
- Quick-connect wiring to any progress fan that accept an accessory light.
- Ideal for bedroom, den or kitchen lighting.
- Includes two 3000K, 800 lumen each (source), Title 24 certified LED bulbs
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Number of Sockets	2
Input Power	10w per socket
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	800/80 (LM-82) per lamp
CCT	3000 K
CRI	90 CRI
Life (hours)	25,000 (L70/TM-21)
FCC	Title 24
Min. Start Temp	-10 °C
Max. Operating Temp	40 °C
Warranty	1 year warranty
Labels	UL Dry location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

P2612-01WB

Images:



Dimensions:

Diameter: 12"
Height: 7-11/16"

Width: 10-3/4"
Height: 6"