



**SPEED SLOT® CARBIDE TIPPED HOLE SAWS**  
 For Drilling Holes in Wood, Steel, Stainless Steel,  
 Cast Iron and Abrasive Metals

**CARBIDE TIP**

**UP TO 50X LIFE**

**UP TO 50X LIFE\***

High performance carbides are welded to the cutting edge for durability and to help prevent tooth loss

**EXTREMELY VERSATILE**

Aggressive tooth design drills through wood, steel, stainless steel, cast iron, fiber cement and plaster

**FAST, EASY PLUG REMOVAL**

SPEED SLOT® staircase design has multiple leverage points for easy plug ejection









**SPEED SLOT®**



\*vs LENOX Bi-Metal Hole Saw cutting cast iron

**APPLICATION**

Nail-Embedded Wood	Steel	Stainless Steel
Drywall / Plaster	Cement Board	Cast Iron
		
		





# SPEED SLOT® CARBIDE TIPPED HOLE SAWS

For Drilling Holes in Wood, Steel, Stainless Steel, Cast Iron and Abrasive Metals

CARBIDE TIP™

UP TO 50X LIFE\*™



1 PER PACK	DIAMETER		PIPE TAP		PIPE ENTRANCE		USE ARBOR			RECOMMENDED RPM				
	PROD NO	IN	MM	IN	MM	IN	MM	SNAP-BACK®	STANDARD	ALUM	STAINLESS STEEL	FIBER-GLASS	CERAMIC TILE	CAST IRON
LXAH31116	11/16	17.5	—	—	—	—	—	5L	1L,4L,5L	1800	690	270	550	240
LXAH334	3/4	19.1	1/2	12.7	3/8	9.5	—	5L	1L,4L,5L	1700	640	250	500	210
LXAH378	7/8	22.2	3/4	19.1	1/2	12.7	—	5L	1L,4L,5L	1500	550	210	430	180
LXAH31	1	25.4	—	—	—	—	—	5L	1L,4L,5L	1300	480	190	370	150
LXAH3118	1-1/8	28.6	1	25.4	3/4	19.1	—	5L	1L,4L,5L	1100	420	170	330	140
LXAH3114	1-1/4	31.8	—	—	—	—	—	2L,6L	2L,3L,6L	1000	380	160	300	130
LXAH3138	1-3/8	34.9	—	—	1	25.4	—	2L,6L	2L,3L,6L	900	350	140	270	110
LXAH3112	1-1/2	38.1	1-1/4	31.8	—	—	—	2L,6L	2L,3L,6L,7L	900	320	120	250	100
LXAH3158	1-5/8	41.3	—	—	—	—	—	2L,6L	2L,3L,6L,7L	700	290	110	230	90
LXAH3134	1-3/4	44.5	1-1/2	38.1	1-1/4	31.8	—	2L,6L	2L,3L,6L,7L	700	270	110	210	90
LXAH32	2	50.8	—	—	1-1/2	38.1	—	2L,6L	2L,3L,6L,7L	600	240	90	190	80
LXAH3218	2-1/8	54.0	—	—	—	—	—	2L,6L	2L,3L,6L,7L	600	220	90	180	70
LXAH3214	2-1/4	57.2	2	50.8	—	—	—	2L,6L	2L,3L,6L,7L	600	210	80	170	70
LXAH3238	2-3/8	60.3	—	—	—	—	—	2L,6L	2L,3L,6L,7L	600	200	80	160	70
LXAH3212	2-1/2	63.5	—	—	2	50.8	—	2L,6L	2L,3L,6L,7L	500	190	70	150	60
LXAH32916	2-9/16	65.1	—	—	—	—	—	2L,6L	2L,3L,6L,7L	500	190	70	140	60
LXAH3258	2-5/8	66.7	2-1/2	63.5	—	—	—	2L,6L	2L,3L,6L,7L	500	180	70	130	60
LXAH321116	2-11/16	68.3	—	—	—	—	—	2L,6L	2L,3L,6L,7L	500	180	60	120	60
LXAH3	3	76.2	—	—	2-1/2	63.5	—	2L,6L	2L,3L,6L,7L	400	160	60	120	50
LXAH3314	3-1/4	82.6	3	76.2	—	—	—	2L,6L	2L,3L,6L,7L	400	150	60	110	50
LXAH3338	3-3/8	85.7	—	—	—	—	—	2L,6L	2L,3L,6L,7L	400	140	60	110	50
LXAH3312	3-1/2	88.9	—	—	—	—	—	2L,6L	2L,3L,6L,7L	400	140	50	110	50
LXAH3358	3-5/8	92.1	—	—	3	76.2	—	2L,6L	2L,3L,6L,7L	400	130	50	100	40
LXAH3334	3-3/4	95.3	3-1/2	88.9	—	—	—	2L,6L	2L,3L,6L,7L	300	130	50	110	40
LXAH34	4	101.6	—	—	—	—	—	2L,6L	2L,3L,6L,7L	300	120	50	100	40
LXAH3418	4-1/8	104.8	—	—	3-1/2	88.9	—	2L,6L	2L,3L,6L,7L	300	120	50	90	40
LXAH3414	4-1/4	108.0	4	101.6	—	—	—	2L,6L	2L,3L,6L,7L	300	110	50	90	40
LXAH3412	4-1/2	114.3	—	—	—	—	—	2L,6L	2L,3L,6L,7L	300	110	40	80	30
LXAH3434	4-3/4	120.7	4-1/2	114.3	4	101.6	—	2L,6L	2L,3L,6L,7L	300	100	40	80	30
LXAH35	5	127.0	—	—	—	—	—	2L,6L	2L,3L,6L,7L	200	100	40	80	30
LXAH3512	5-1/2	139.7	—	—	—	—	—	2L,6L	2L,3L,6L,7L	200	100	40	70	30
LXAH36	6	152.4	—	—	—	—	—	2L,6L	2L,3L,6L,7L	100	80	30	60	30

Note: We recommend the use of a carbide tipped pilot drill when cutting hard materials. Bits available in standard and long lengths—3 1/4" (83mm) LXAH9314CTPB and 4 1/4" (108mm) LXAH9414CTPB.

\*vs LENOX Bi-Metal Hole Saw cutting cast iron

### PLUMBER'S KIT



**LXAH3PSET6  
8 PIECE**  
3/4", 7/8", 1-1/8",  
1-1/2", 1-3/4", 2-1/4"  
Arbors: 1L, 2L  
MEDIUM KIT

### ELECTRICIAN'S KIT



**LXAH3LSET6  
8 PIECE**  
7/8", 1-1/8", 1-3/8",  
1-3/4", 2", 2-1/2"  
Arbors: 1L, 2L  
MEDIUM KIT

### CONTRACTOR'S KIT



**LXAH3GSET11  
15 PIECE**  
3/4", 7/8", 1", 1-1/8", 1-1/4",  
1-3/8", 1-1/2", 1-3/4", 2",  
2-9/16", 3". Arbors: 1L, 2L  
Two pilot drills  
LARGE KIT