

RESIDENTIAL ELECTRIC WATER HEATERS

# PROLINE® SPECIALTY ELECTRIC

COMMERCIAL-GRADE RESIDENTIAL

### **TABLE TOP**

• Features a convenient flat porcelain surface at 36" height, providing extra "counter space" wherever installed. All plumbing and electrical connections are made through the back of the water heater. This heater is equipped with a PEX cross-linked polymer dip tube.

### POINT-OF-USE

• Designed for low-demand, such as office lavatories or buildings with remote restrooms.

### **COMPACT**

• Side-mounted plumbing and electrical connections (optional top-mounted water connections for field conversion). Designed for installation under a counter, in a crawl space or in other tight spaces.

# **BLUE DIAMOND® GLASS COATING**

 Provides superior corrosion resistance compared to industry standard glass linina.

# **ENHANCED-FLOW BRASS DRAIN VALVE**

- Our standard residential water heaters have a solid brass, tamper resistant, enhanced-flow, ball type, drain valve.
- Uses a standard female hose fitting that allows for fast and easy draining during maintenance.
- Designed for easy operation, this valve includes an integral screwdriver slot that features a 1/4 turn (open/close) radius, which not only permits full straightthrough water flow but also a quick and positive shut off.

#### CODE COMPLIANCE

- Meets UBC, CEC and HUD National Codes.
- Meets the thermal efficiency and standby loss requirements of the U.S. Department of Energy and current edition of ASHRAE/IES 90.1.
- Complies with the Federal Energy Conservation Standards effective April 16, 2015, in accordance with the Energy Policy and Conservation Act (EPCA), as amended.

### APPROVED FOR MANUFACTURED HOUSING

• All residential electric water heaters are compliant with HUD standards for mobile homes/manufactured housing.

# CERTIFIED TO UL 174 FOR HOUSEHOLD ELECTRIC WATER HEATERS

# CSA CERTIFIED AND ASME RATED T&P **RELIEF VALVE**

# **DESIGN-LISTED BY UNDERWRITERS LABORATORIES**

- Certified at 300 psi test pressure and 150 psi working pressure.
- Listed according to UL 174 standards governing storage tank-type electric water heaters.

# 6-YEAR LIMITED TANK AND PARTS WARRANTY

• For complete information consult the written warranty or go to hotwater.com.












Model Number	Nominal Capacity	Rated Storage Volume	First Hour Rating (Gallons)	UEF	Element Wattage		Recovery @ 90 °F Rise	Dimensions in Inches			Approx.
					Standard	Maximum	Gallons Per Hour	Α	В	С	Shipping Weight (lbs)
Compact Models					120V	240V					
EJC-6	6	6	N/A	N/A	1650	3000	8	15-1/4	10-3/4	14-1/4	35
EJC-10	10	9	N/A	N/A	1650	6000	8	18-1/4	12-1/4	16	41
EJCS-20	19	17	N/A	N/A	2500	6000	11	24-3/4	18-5/8	18	68
EJCT-20	19.9	18	N/A	N/A	2500	6000	11	31-5/8	25-3/4	16	68
Lowboy Side-Connect Model					240V						
ENJB-30*	28	26	47	0.90	4500	6000	21	30	21-3/4	22	101
ENJ-30	28	26	43	0.91	4500	6000	21	31-1/4	21-3/4	24	115
ENJB-40*	38	35	57	0.94	4500	6000	21	31-3/4	24	24	118
ENJB-40W*	38	35	38	0.91		4000	18	31-3/4	24	24	118
ENJ-40	38	35	54	0.93	4500	6000	21	33-1/2	24	26	118
ENJ-40W	38	35	38	0.91		4000	18	33-1/2	24	26	118
Table Top Model					240V						
ENTT-38	38	35	55	0.90	4500	5500	21	36	24	25	150
Point-Of-Use-Models					120V						
EMT-2.5	2.5	2.6	N/A	N/A	1440 @ 120V		7	14-1/2	10-3/8	11-3/4	17
EMT-4	4	3.8	N/A	N/A	1440 @ 120V		7	19-1/4	10-3/8	11-3/4	20
EMT-6	6	5.9	N/A	N/A	1440 @ 120V		7	20	12-1/2	13-3/4	24


<sup>\*</sup>Models ship with a supplied insulation blanket.

When ordering models ENJ-40 or ENJB-40 the model number will change for wattages of 4kW to 1kW. The new model number will include a "W" suffix (example: ENJB-40W) Dimensions and specifications subject to change without notice in accordance with our policy of continuous product improvement.


Top mounted T&P adds approximately 3" to overall installation height.


Water connection is 3/4" on Table Top and Compact models and 1/2" NPT on Point-Of-Use Models





ENJ-30, ENJB-30 **ENJ-40, ENJB-40** 





For Technical Information, call 800-527-1953. A. O. Smith Corporation reserves the right to make product changes or improvements without prior notice.