1/2" x 520"



STANDARD DENSITY PTFE PIPE THREAD TAPE

Product Features

Chemical Properties: >99.5% Polytetrafluoroethylene

Tape Color: **Bright White** 0.0035"

Thickness (+.0005/-.0005):

Available widths: 1/2" (12.7mm) 3/4" (19.1mm)

1" (25.4mm)

Available lengths: 260" (660cm) 520" (1321cm)

Elongation (+/- 2%): Minimum of 50%

Density (+/- 5%): 0.4 g/cm3 Pressure Rating: up to 10,000psi

Temperature: -450°F to 500°F (-268°C to 260°C)

Standards/Approvals: MIL Spec T-27730A

Incompatibilities: Avoid using with Molten Alkali, Halogen and Fluorine products at high

temperature and pressure. Not for use on liquid fuels such as gasoline or diesel.

Usage: To be used on all types of threaded fittings for passage of potable and non potable water,

most chemicals, oxygen, hydraulic lines, and high-pressure lines up to 1-1/2" in diameter.

Unlimited

China Shelf Life:

Country of Origin:

Usage

To be used on all types of threaded fittings for passage of potable and non potable water, most chemicals, oxygen, hydraulic lines, and high-pressure lines not exceeding 1-1/2" in diameter

Product Specifications

| White Standard Density PTFE Thread Tape | Width | Length |
|---|---------------|---------------|
| PSTTD260 | 1/2" (12.7mm) | 260" (660cm) |
| PSTTD520 | 1/2" (12.7mm) | 520" (1321cm) |
| PSTTF260 | 3/4" (19.1mm) | 260" (660cm) |
| PSTTF520 | 3/4" (19.1mm) | 520" (1321cm) |
| PSTTG520 | 1" (25.4mm) | 520" (1321cm) |

Warranty and Codes

This PROSELECT product carries a 1-year limited warranty.