


BENNETT

SINGLE-HOLE OUTDOOR KITCHEN FAUCET

SKU: 433135



FEATURES

Max. Countertop Thickness: 1-7/8"
Faucet Centers: Single-Hole
Length: 5-1/8"
Width: 10"
Height: 11-1/2"
Height To Spout: 10-1/4"
Spout Reach: 8-3/8"
Swivel Spout: Yes
Base Plate Length: 2-1/8"
Base Plate Width: 2-1/8"
Handle Length: 3-7/8"
Height to Bottom of Handle: 1-1/2"
Ceramic Disc Cartridges: Yes
Hot and Cold Indicators: Yes
IPS: 1/2
Maximum Flow Rate: 1.8 gpm
(gallons per minute)

CODES/STANDARDS

cUPC
ASME A112.18.1/CSA B125.1
NSF/ANSI 61
NSF/ANSI 372
CEC Listed



SIGNATURE HARDWARE LIFETIME WARRANTY

See website for warranty information



All product dimensions are nominal.

REVISED 07/09/2019