60"x32" BRADENTON

ACRYLIC ALCOVE TUB

SKU: 948254



CONTENTS

AIR & WHIRLPOOL TUB	 PAGE 2
60" X 32" TUB	 PAGE 3

FEATURES

Tub Options:

Soaking - No air feature.

Air - 65 Air jets circulate warm air throughout the tub, creating warm bubbles for a massaging, rejuvenating experience.

Whirlpool - 8 Strategically placed air jets move water with increased pressure for an invigorating bathing experience. Total Massage: A combination of air and whirlpool systems that creates a spa-like experience of ultimate relaxation and targeted massage.

One three-speed air switch for air bath.

65 Air jets circulate warm air throughout the tub, creating warm bubbles for a massaging, rejuvenating experience. Air Bath system uses a 7.5 amp, 600 watt heated blower for air bath system.

One single-speed air switch for whirlpool.

8 Strategically placed air jets move water with increased pressure for an invigorating bathing experience.

Whirlpool system uses a powerful 1.75hp, 10.9 amp whirlpool pump.

Two air switch actuators for total massage.

Integral tile flange and skirt with removable access panel (exception: solid skirt on soaker tub).

Safety Suction meets all requirements of durability and clog-resistance through standard testing.

Pre-wired for simple plug-in installation.

ABS drain version available if needed for your installation. Optional Quick Connect Drop-In Drain Kit Includes: Floor Plate, 1-1/2" PVC Pipe, 2" x 1-1/2" Trap Adapters, 1 Brass Threaded, 1 Brass Unthreaded Tailpiece and Plug. Installs above your subfloor, but underneath your cement floor or tile, so you do not need access below the fixture.

SIGNATURE HARDWARE Lifetime Warranty

See website for detailed warranty information.

REVISED 01/15/2020

CODE: SHBDA6032LWH/SHBDA6032RWH/SHBDS6032LWH/SHBDS6032RWH/SHBDT6032LWH/SHBDT6032RWH SHBDW6032LWH/SHBDW6032RWH/SHBDA6032LBS/SHBDA6032RBS/SHBDS6032LBS/SHBDS6032RBS/SHPRESSHTR



R TUB AND WHIRLPOOL

COMPONENTS LIST

- Powerful whirlpool pump with variable flow device
- Heated blower for air bath system

INSTALLATION

- Whirlpool and Total Massage units require dedicated 20 Amp, 120V service
- You must provide a receptacle with a 20 Amp configuration
- Electrical outlet must be mounted 4" (101mm) above the floor line and 12" max (305mm) inside from the edge of the bathtub, or in accordance with local building and electrical codes

INTEGRATED CONTROL PANEL


- Whirlpool Baths: Equipped with on/off switch actuator. Each depression of the switch will activate the pump
- Air Baths: Equipped with a 3-speed air switch actuator. Each depression of the switch will change the flow of air
- Total Massage Baths: Equipped with both an on/off air switch actuator for whirlpool function and 3-speed air switch actuator for air function

INSIDE OF BATH

- (8) HIGH-FLOW DIRECTIONAL AND VOLUME-ADJUSTABLE WHIRLPOOL JETS
- (65) CHANNEL-FED AIRJETS (air bath and total massage)




WHIRLPOOL JET




ELECTRICAL CONFIGURATIONS

WHIRLPOOL WITH INSTALLED AIR SWITCH TOTAL MASSAGE CIRCUIT WITH OPTIONAL HEATER



AIR BATH CIRCUIT




PAGE 2





60"x32" BRADENTON

ACRYLIC ALCOVE SOAKING TUB

SKU: 948254







FEATURES

Product Finish: White Overflow Hole: Yes Shape: Rectangle Material: Acrylic Length: 60" Width: 32" Height: 21-1/2" Tub Interior Length: 40-1/2" Tub Interior Width: 20" Water Depth To Overflow: 17-1/2" Drain Included: Optional Drain Placement: End Faucet Included: No Water Capacity (Gallons): 48 Tub Weight Uncrated (lbs): 87 Tub Weight Crated (lbs): 197

SIGNATURE HARDWARE LIFETIME WARRANTY

See website for warranty information



PAGE 3

All dimensions and specifications are nominal and may vary. Use actual products for accuracy in critical situations.



Textured slip-resistant bottom.

All dimensions (± 1/2"). Integral arm rests.

Pre-leveled base.