



CONTEMPORARY

LOW PROFILE RAINFALL SHOWER HEAD

SKU: 948945



Product Code	Reference A	Max Flow-Rate
SHRS820RG	8" (203 mm)	1.8 gpm (6.8L/min) max @ 80 psi
SHRS825R	8" (203 mm)	2.5 gpm (9.5L/min) max @ 80 psi
SHRS1020RG	10" (254 mm)	1.8 gpm (6.8L/min) max @ 80 psi
SHRS1025R	10" (254 mm)	2.5 gpm (9.5L/min) max @ 80 psi
SHRS1225R	12" (305 mm)	2.5 gpm (9.5L/min) max @ 80 psi

FEATURES

- Shape: Round
- Material: Stainless Steel
- Features: Shower Head Only
- Height: 2-1/2"
- Shower Head Spray: Rainfall
- Shower Head Swivel: Yes
- Single Function Shower Head (Full Spray)
- Easy Clean Silicon Nozzles
- Brass Ball Joint
- IPS: 1/2"

CODES/STANDARDS

SHRS820RG/SHRS1020RG

- cCSAus
- ASME A112.18.1/CSA B125.1
- WaterSense
- CEC Listed
- Massachusetts Accepted



SHRS825R/SHRS1025R/SHRS1225R

- cCSAus
- ASME A112.18.1/CSA B125.1
- Massachusetts Accepted



SIGNATURE HARDWARE LIFETIME WARRANTY

See website for warranty information



All dimensions and specifications are nominal and may vary. Use actual products for accuracy in critical situations.

REVISED 01/03/2020
Code: SHRS820RGBN/SHRS820RGCP
SHRS825RBN/SHRS825RCP
SHRS1020RGBN/SHRS1020RGCP
SHRS1025RBN/SHRS1025RCP
SHRS1225RBN/SHRS1225RCP