PENDLETON

PRESSURE BALANCE TUB AND SHOWER SET

SKU: 948672



FEATURES

Material: Brass Shape: Round Handle Type: Lever Assembly Required: No Installation Type: Wall Shower Head Material: ABS Shower Head Spray: Single Function Shower Arm Included: Yes Shower Head Swivel: Yes Diverter Included: Yes Metal Handle Tub Spout Diverter Slip-Fit Tub Spout Extension Kit Available: ACF4001EXT Optional Rough-in Valve Shower Head Flow Rate: 1.8 gpm (6.8L/min) max @ 80 psi

SIGNATURE HARDWARE Lifetime Warranty

See website for detailed warranty information.

CONTENTS


SHOWER SET	 PAGE 2
VALVE	 PAGE 3


REVISED 01/15/2020

PENDLETON

PRESSURE BALANCE TUB AND SHOWER SET

SKU: 948672





FEATURES

Shower Head Diameter: 4-1/16" Shower Head IPS: 1/2" Tub Filler Spout Reach: 5-1/4" Valve Trim Width: 6-3/4" Valve Trim Height: 6-3/4" NPT Connection: 1/2"

CODES/STANDARDS

cUPC ASME A112.18.1/CSA B125.1 ICC/ANSI A117.1 (when installed according to ADA standards) WaterSense CEC Listed Massachusetts Accepted



SIGNATURE HARDWARE LIFETIME WARRANTY

See website for warranty information



PAGE 2 Code: SHPT8030GBN SHPT8030GCP/SHPT8030GPN


All dimensions and specifications are nominal and may vary. Use actual products for accuracy in critical situations.



PENDLETON

OPTIONAL PRESSURE BALANCE TUB AND SHOWER ROUGH IN VALVE

SKU: 948672



FEATURES

ÍSI

Pressure Balance Valve With Integral Stops One-Piece Cartridge Design For Ease Of Maintenance Back-To-Back Capability Ceramic Disc Valve Cartridge Cast Bronze Valve Body Adjustable Temperature Limit Stop Quick Remove Plaster Guard Easy Mounting Brackets

CODES/STANDARDS

cUPC ASME A112.18.1/CSA B125.1 Massachusetts Accepted

SIGNATURE HARDWARE LIFETIME WARRANTY See website for warranty information





All dimensions and specifications are nominal and may vary. Use actual products for accuracy in critical situations.

PAGE 3 Code: SH4001