TRADITIONAL

ROUND RAINFALL SHOWER HEAD WITH EXTENDED SHOWER ARM

SKU: 949069



CONTENTS

SHOWER HEAD PAGE 2 SHOWER ARM PAGE 3

FEATURES

Shape: Round

Assembly Required: No Installation Type: Wall Shower Arm Included: Yes

Single Function Shower Head (Full Spray)

Shower Head Spray: Rainfall Shower Head Swivel: Yes Escutcheon Included: Yes Easy Clean Rubber Nozzles

Brass Ball Joint

SIGNATURE HARDWARE Lifetime Warranty

See website for detailed warranty information.


REVISED 01/07/2020




TRADITIONAL

ROUND RAINFALL SHOWER HEAD

SKU: 949069





Product Code	Reference A	Max Flow-Rate
SHRS820TG	8" (203 mm)	1.8 gpm (6.8L/min) max (a) 80 psi
SHRS825T	8" (203 mm)	2.5 gpm (9.5L/min) max (a) 80 psi
SHRS1020TG	10" (254 mm)	1.8 gpm (6.8L/min) max @ 80 psi
SHRS1025T	10" (254 mm)	2.5 gpm (9.5L/min) max @ 80 psi

FEATURES

Material: Stainless Steel Height: 2-1/2" IPS: 1/2"

CODES/STANDARDS

SHRS820TG/SHRS1020TG

cUPC ASME A112.18.1/CSA B125.1 CEC Listed



SHRS825T/SHRS1025T

cUPC ASME A112.18.1/CSA B125.1



SIGNATURE HARDWARE LIFETIME WARRANTY

See website for warranty information



PAGE 2 Code: SHRS820TGBN SHRS820TGCP/SHRS820TGPN SHRS825TBN/SHRS825TCP/SHRS825TPN SHRS1020TGBN/SHRS1020TGCP/SHRS1020TGPN SHRS1025TBN/SHRS1025TCP/SHRS1025TPN


 $All\ dimensions\ and\ specifications\ are\ nominal\ and\ may\ vary.\ Use\ actual\ products\ for\ accuracy\ in\ critical\ situations.$



TRADITIONAL

EXTENDED SHOWER ARM

SKU: 949069



FEATURES

Material: Brass Height: 1-9/16" Base Plate Diameter: 2-3/8" IPS: 1/2"

CODES/STANDARDS

cCSAus ASME A112.18.1/CSA B125.1 Massachusetts Accepted

SIGNATURE HARDWARE LIFETIME WARRANTY

See website for warranty information



PAGE 3 Code: SHRSA120BN/SHRSA120CP/SHRSA120PN SHRSA180CP/SHRSA180PN/SHRSA180BN

All dimensions and specifications are nominal and may vary. Use actual products for accuracy in critical situations.

