



# MODERN

## SQUARE RAINFALL SHOWER HEAD WITH ROUNDED CORNERS

SKU: 948947



Product Code	Reference A	Max Flow-Rate
SHRS820SG	8" (203 mm)	1.8 gpm (6.8L/min) max @ 80 psi
SHRS825S	8" (203 mm)	2.5 gpm (9.5L/min) max @ 80 psi
SHRS1020SG	10" (254 mm)	1.8 gpm (6.8L/min) max @ 80 psi
SHRS1025S	10" (254 mm)	2.5 gpm (9.5L/min) max @ 80 psi
SHRS1225S	12" (305 mm)	2.5 gpm (9.5L/min) max @ 80 psi

### FEATURES

- Shape: Square
- Material: Stainless Steel
- Features: Shower Head Only
- Height: 2-1/2"
- Shower Head Spray: Rainfall
- Shower Head Swivel: Yes
- Single Function Shower Head (Full Spray)
- Easy Clean Rubber Nozzles
- Brass Ball Joint
- IPS: 1/2"

### CODES/STANDARDS

- SHRS820S/SHRS1020SG
- cCSAus
  - ASME A112.18.1/CSA B125.1
  - WaterSense
  - CEC Listed
  - Massachusetts Accepted



- SHRS825S/SHRS1025S/SHRS1225S
- cCSAus
  - ASME A112.18.1/CSA B125.1
  - Massachusetts Accepted



### SIGNATURE HARDWARE LIFETIME WARRANTY

See website for warranty information



All dimensions and specifications are nominal and may vary. Use actual products for accuracy in critical situations.

REVISED 01/03/2020  
Code: SHRS820SGBN/SHRS820SGCP  
SHRS825SBN/SHRS825SCP/SHRS1020SGBN  
SHRS1020SGCP/SHRS1025SBN/SHRS1025SCP  
SHRS1225SBN/SHRS1225SCP