

CONTEMPORARY

LOW PROFILE SHOWER HEAD WITH CEILING-MOUNT ARM

SKU: 949067



FEATURES

- Shape: Round
- Installation Type: Ceiling Mount
- Shower Head Spray: Single Function (Full Spray)
- Shower Arm Included: Yes
- Shower Head Swivel: Yes
- Easy Clean Rubber Nozzles
- Brass Ball Joint
- Escutcheon Included: Yes

SIGNATURE HARDWARE Lifetime Warranty

See website for detailed warranty information.

CONTENTS



SHOWER HEAD	PAGE 2
SHOWER ARM	PAGE 3

REVISED 01/07/2020

CONTEMPORARY

LOW PROFILE SHOWER HEAD

SKU: 949067



Product Code	Reference A	Max Flow-Rate
SHRS820RG	8" (203 mm)	1.8 gpm (6.8L/min) max @ 80 psi
SHRS825R	8" (203 mm)	2.5 gpm (9.5L/min) max @ 80 psi
SHRS1020RG	10" (254 mm)	1.8 gpm (6.8L/min) max @ 80 psi
SHRS1025R	10" (254 mm)	2.5 gpm (9.5L/min) max @ 80 psi
SHRS1225R	12" (305 mm)	2.5 gpm (9.5L/min) max @ 80 psi

FEATURES

Material: Stainless Steel
 Height: 2-1/2"
 IPS: 1/2"

CODES/STANDARDS

SHRS820RG/SHRS1020RG
 cCSAus
 ASME A112.18.1/CSA B125.1
 WaterSense
 CEC Listed
 Massachusetts Accepted



SHRS825R/SHRS1025R/SHRS1225R
 cCSAus
 ASME A112.18.1/CSA B125.1
 Massachusetts Accepted



SIGNATURE HARDWARE LIFETIME WARRANTY

See website for warranty information




All dimensions and specifications are nominal and may vary. Use actual products for accuracy in critical situations.

PAGE 2
 Code: SHRS820RGBN/SHRS820RGCP
 SHRS825RBN/SHRS825RCP
 SHRS1020RGBN/SHRS1020RGCP
 SHRS1025RBN/SHRS1025RCP
 SHRS1225RBN/SHRS1225RCP

CONTEMPORARY

CEILING-MOUNT SHOWER ARM

SKU: 949067



FEATURES

Material: Brass
Base Plate Diameter: 2-3/8"
IPS: 1/2"

CODES/STANDARDS

SHRSC40/SHRS120
cCSAus
ASME A112.18.1/CSA B125.1
Massachusetts Accepted
SHRSC60
cCSAus
ASME A112.18.1/CSA B125.1

SIGNATURE HARDWARE LIFETIME WARRANTY

See website for warranty information



All dimensions and specifications are nominal and may vary. Use actual products for accuracy in critical situations.

PAGE 3
Code: SHRSC40BN/SHRSC40CP/SHRSC60BN
SHRSC60CP/SHRSC120BN/SHRSC120CP