

ROUND RAINFALL SHOWER HEAD

SKU: 948948





Procuct Code	Reference A	Max Flow-Rate
SHRSB620RG	6" (152 mm)	1.8 gpm (6.8L/min) max @ 80 psi
SHRSB625R	6" (152 mm)	2.5 gpm (9.5L/min) max (a) 80 psi
SHRSB820RG	8" (203 mm)	1.8 gpm (6.8L/min) max @ 80 psi
SHRSB825R	8" (203 mm)	2.5 gpm (9.5L/min) max (a) 80 psi

FEATURES

Shape: Round Material: ABS Features: Shower Head Only Height: 2-1/16" Shower Head Spray: Rainfall Shower Head Swivel: Yes Single Function Shower Head (Full Spray) Easy Clean Silicon Nozzles Brass Ball Joint IPS: 1/2"

CODES/STANDARDS

SHRSB620RG/SHRSB820RG

cUPC ASME A112.18.1/CSA 125.1 WaterSense Massachusetts Accepted





SHRSB625R/SHRSB825R

cUPC ASME A112.18.1/CSA B125.1 Massachusetts Accepted



REVISED 01/03/2020 Code: SHRSB620RGBN/SHRSB620RGCP SHRSB625RBN/SHRSB625RCP SHRSB820RGBN/SHRSB820RGCP SHRSB820GPN/SHRSB825RBN SHRSB825RCP/SHRSB825RPN

SIGNATURE HARDWARE

See website for warranty information

LIFETIME WARRANTY

All dimensions and specifications are nominal and may vary. Use actual products for accuracy in critical situations.

