

# CARRAWAY

## 4-HOLE ROMAN TUB FILLER AND HAND SHOWER

SKU: 948678



### FEATURES

- 4-hole installation.
- Spout max. flow rate: 12.7 gpm (48.1L/min) max @ 80 psi.
- Hand shower max. flow rate: 1.8 gpm (6.8 L/min) @ 80 psi.
- Lift rod diverter to handshower.
- Handshower includes factory installed backflow prevention check valve.
- Optional rough-in valve:
- Brass coupling nut.
- Accommodates an 8" - 16" faucet spread.
- Deck thickness max. 1.5" or screws can be removed to accommodate thicker deck installations up to 2".

### SIGNATURE HARDWARE Lifetime Warranty

See website for detailed warranty information.

### CONTENTS


TUB FILLER .....	PAGE 2
VALVE .....	PAGE 3

REVISED 01/15/2020

# CARRAWAY

## 4-HOLE ROMAN TUB FILLER AND HAND SHOWER

SKU: 948678



### FEATURES

Installation Type: Deck Mount  
 Handle Type: Lever  
 Max. Deck Thickness: 2"  
 Tub Faucet Material: Brass  
 Length: 13-1/2"  
 Width: 9-3/4"  
 Height: 8-1/8"  
 Height To Spout: 4-1/4"  
 Spout Reach: 8"  
 Spout Width: 1-1/2"  
 Hot and Cold Indicators: No  
 Drain Included: No  
 Base Plate Length: 2-1/8"  
 Base Plate Width: 2-1/8"  
 Ceramic Disc Cartridges: Yes  
 Hand Shower Hose Length: 61"  
 Hand shower flow rate: 1.75 gpm.

### CODES/STANDARDS

cUPC  
 ASME A112.18.1/CSA B125.1  
 ASME A112.18.3  
 ADA Compliant (when installed according to  
 ADA Standards)  
 CEC Listed



### SIGNATURE HARDWARE LIFETIME WARRANTY

See website for warranty information



PAGE 2


Code: SHCR4RTGPN/SHCR4RTGCP  
 SHCR4RTGBN/SH674164

All dimensions and specifications are nominal and may vary. Use actual products for accuracy in critical situations.

# 4 HOLE

## OPTIONAL ROMAN TUB FILLER ROUGH-IN VALVE

SKU: 448005



### FEATURES

- Fits 4-hole
- Brass coupling nut Trim sold separately
- Flow rate: 8 GPM at 20 PSI
- Deck thickness max. 1.5" or screws can be removed to accommodate thicker deck installations up to 2"
- Replacement cartridges available -  
HOT MIR3357027H and  
COLD MIR3357027C

### CODES/STANDARDS

- cUPC
- ASME A112.18.1/CSA B125.1
- ANSI A117.1 (when installed according to ADA standards)
- Massachusetts Accepted

### SIGNATURE HARDWARE LIFETIME WARRANTY

See website for warranty information



All dimensions and specifications are nominal and may vary. Use actual products for accuracy in critical situations.

PAGE 3  
CODE: SH674164