IMROCK SLIDING TUB DC

SKU: 949145

BEFORE YOU BEGIN

We recommend consulting a professional if you are unfamiliar with installing plumbing fixtures. Signature Hardware accepts no liability for any damage to the tub, wall, or for personal injury during installation.

Observe all local plumbing and building codes.

Unpack and inspect the product for shipping damage. If any damage is found, contact our Customer Relations team at 1-866-855-2284.

GETTING STARTED

• Ensure that you have gathered all the required materials that are needed for the installation.

BEFORE INSTALLATION

For these instructions, it is assumed that the tub and finished walls/tile are in place

Tub threshold needs to have a flat surface of 2-3/4".

Not recommended for cast iron or enameled steel tubs.

TOOLS AND MATERIALS:







Hacksaw

Phillips Screwdriver







Safety Glasses

Tape Measure

Level







Silicone Sealant (100% Neutral Cure)

Cuttina Pliers






1/4" Drill Bit 1/8" Drill Bit

REVISED 01/09/2020 CODES: 525119, 525120, 525122, 525123, 528311, 528312


SKU: 949145

Note: Every step applies to both the left side assembly and the right side.



SKU: 949145


PART LIST




SKU: 949145

INSTALLATION

1. Locate the center of the tub rim, draw and mark the installation hole and position line of door guide (19). Be sure that there is equal distance both from left to right and front to back on tub rim. Drill installation hole with 1/8" drill bit. Attach door guide (19) to rim with 1-1/4" screw (8).




2. Disassemble the rail wall bracket kit (7) as shown. The mounting bracket kit (7) should be mounted 7/8" back from edge of door guide (19). The mounting bracket should be mounted 59-1/2" from the tub rim as shown. Drill installation hole with 1/4" drill bit. Apply a small amount of silicone sealant to the installation hole, then insert wall anchor (6). Attach rail wall bracket against the wall with 1-1/4" screw (8).




SKU: 949145


3. Insert top rail (9) into rail wall bracket (7). Using a level, ensure top rail is leveled.. Install rail into rail wall bracket (7) with allen key (21).


Note: Minimum measurement for brackets and rail is 58", some trimming of the rail may be necessary depending on your installation.






4. Install threshold gasket (17) at the bottom of inner door (3). Using cutting pliers, trim the top 4-3/4" strip of the water-retaining gasket (18). Be sure to not cut the U-shaped portion of the gasket. Install water-retaining gasket (18) on inner glass.







SKU: 949145

5. Disassemble double roller (10) as shown. Install the double roller onto the slot of the top rail.(9).




6. Insert inner door (3) onto the door guide (19) slot. Attach the inner door panel (3) to the top rail (9) with the double roller (10). Tighten the hexagonal nut with spanner (20).






SKU: 949145

7. Make sure 180° magnet seal short (2) and the magnetic aluminum (1) attract to each other, adjusting the roller if there is any gap. Attach 180° magnet seal short (2) to inner door (3) and slide close. Mark position of the magnetic aluminum (1) at the wall. Remove magnetic alluminum (1) from 180° magnet seal short (2) Position magnetic alluminum (1) on mounting line and mark the mounting hole. Drill installation hole using 1/4" drill bit. Apply a small amount of silicone sealant to the installation hole and insert the wall anchor. Attach magnetic aluminum (1) to the wall with screw 1-1/4" (4).




8. Install roller (11) on outer door (13), then tighten with spanner. Install threshold gasket (17) at the bottom of outer door (13). Using cutting pliers, trim the top 4-3/4" strip of the water-retaining gasket (18). Be sure to not cut the U-shaped portion of the gasket. Install water-retaining gasket (18) on outer glass (13).




LIMROCK SLI<u>DING TUB DOOR</u>

SKU: 949145

9. Install outer door (13) onto the top rail (9). Using level, ensure outer door (13) is leveled.




10. Install anti-jumper (12) on outer door (13). Install handle (5) on doors (3/13) as shown.




SKU: 949145

11. Make sure 180° magnet seal short (2) and the magnetic aluminum (1) attract to each other, adjusting the roller if there is any gap. Attach 180° magnet seal short (2) to outer door (13) and slide close. Mark position of the magnetic aluminum (1) at the wall. Remove magnetic alluminum (1) from 180° magnet seal short (2) Position magnetic alluminum (1) on mounting line and mark the mounting hole. Drill installation hole using 1/4" drill bit. Apply a small amount of silicone sealant to the installation hole and insert the wall anchor. Attach magnetic aluminum (1) to the wall with screw 1-1/4" (4).



12. Note distance from wall to door guide (19), then cut threshold (16) to your noted distance less 1/2". Mark a hole for the threshold cover (15) for installation. Drill installation hole with 1/8" drill bit. Attach threshold cover (15) to tub rim with 1-1/4" screw (8).



SKU: 949145

13. Apply a continuous bead of silicone sealant to sliding door assembly. Do not open or close for 24 hours while sealant cures.

