


RWHWB8-NC - R SERIES 8" NATURAL COPPER WALL BRACKET



W: 8"
H: 11¼"
Ext: 11"

Removable Stainless Steel
Wire Guard Included

Dimensions

Width 8"
Height 11¼"
Extension 11"

Finish & Material

Finishes **NC** - Natural Copper
Material Natural Copper

Wire Guard

Wire Guard Stainless Steel

Wattage

Bulbs 1-Medium A19
Watts per Bulb 100W
Voltage 120V


Certification

UL Listed Wet Location

Item Number

SKU RWHWB8-NC

RWHWB8 - R SERIES 8" WALL BRACKETS



W: 8"
H: 11¼"
Ext: 11"

Removable Wire Guard
Included

Dimensions

Width 8"
Height 11¼"
Extension 11"

Finish & Material

Finishes **ABR** - Architectural Bronze
GA - Galvanized
SB - Satin Black
SG - Satin Green
SR - Satin Red
WH - White

Material Cold Rolled Steel &
Die-Cast Zinc

Wire Guard

Wire Guard Steel

Wattage

Bulbs 1-Medium A19
Watts per Bulb 100W
Voltage 120V

Certification

UL Listed Wet Location

Item Number

SKU RWHWB8

Note: All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.