

# **FAIRFIELD**

# **Widespread Lavatory Faucet**











### • 3-5/16" (8.4 cm) spout height at outlet • 6-15/16" (17.6 cm) spout reach (c-c)

Spout assembly with integral supply hoses

- For 8" (20.3 cm) centers Maximum 20" (50.8 cm)
- 1.5 gallons (5.7 liters) per minute maximum flow rate

• Quarter-turn washerless ceramic disc valve cartridges

# **Codes / Standards Compliance**

Meets or exceeds the following at date of manufacture:

- ASME A112.18.1/CSA B125.1
- IAPMO/cUPC

**Features** 

Brass valve bodies

· Solid brass construction

ADA compliant handles

• Pop-up drain with tailpiece

- IPC
- NSF 61
- ADA
- ICC/ANSI A117.1
- Energy Policy Act of 1992
- All applicable US Federal and State material regulations
- EPA WaterSense<sub>®</sub>



### **Colors / Finishes**

• 10B: Oil Rubbed Bronze • 15: Polished Nickel • 15S: Satin Nickel • 26: Polished Chrome

• Other: Refer to the Newport Brass catalog for additional color/finish options.

#### **Specified Model Colors / Finishes** Model **Description** 1000 Widespread Lavatory Faucet Other $\square$ 10B $\square$ 15 $\square$ 15S $\square$ 26

## **Product Specification:**

#### Add "Color / Finish" suffix to Model number, below.

The two-handle Widespread Lavatory Faucet shall be made of solid brass construction. Faucet shall feature brass valve bodies. Faucets shall feature quarter-turn washerless ceramic disc valve cartridges. Faucet shall have a 1.5 gallon (5.7 L) per minute maximum flow rate. Product shall be for 8" centers (20.3 cm) - Maximum 20" (50.8 cm). Product shall have a 3-5/16" (8.4 cm) spout height at outlet, 6-15/16" (17.6 cm) spout reach (c-c), include a pop-up drain with tailpiece and ADA compliant handles. Faucet shall be Newport Brass Model 1000/\_\_

# **Product Dimensions** (units are in inches)



