

UC-24BG/S



FEATURES


- Controls temperature within one degree of setpoint
- Locks in cold air to ensure freshness with magnetic door seals
- Store seven 750-ml wine bottles on each smooth roller-glide shelf
- Keeps dairy, produce, and other perishables at their optimal temperature
- Control brightness of interior
- Display beverages via a single, triple-pane and UV-resistant glass door
- Gain storage flexibility with one stationary and two adjustable shelves
- Locate items quickly with clear storage bin

ACCESSORIES

- Cocoa Black Rear Wall
- Dual Installation Kit
- Glass Shelf
- Undercounter Black Dual Kickplate
- Undercounter Door Lock Kit
- Undercounter Dual Lock Kit
- Undercounter Silver Dual Kickplate
- Undercounter Silver Kickplate
- Undercounter Solid Overlay Door

Wine Rack

Accessories are available through an authorized dealer.
For local dealer information, visit subzero-wolf.com/locator.



HANDLE OPTIONS

PRO



TUBULAR



PRODUCT DETAILS


REFRIGERATOR

- 1 adjustable wine storage rack
- 3 glass shelves (2 adjustable; 1 stationary)
- 1 storage bin

PRODUCT SPECIFICATIONS


Model	UC-24BG/S
Dimensions	23 7/8"W x 34"H x 24"D
Door Clearance	23 3/8"
Weight	130 lbs
Refrigerator Capacity	6 cu. ft.
Electrical Supply	115 VAC, 60 Hz
Electrical Service	15 amp dedicated circuit
Wine Storage Capacity	8 Bottles

ELECTRICAL




NOTE: Dimensions in parenthesis are in millimeters unless otherwise specified

INTERIOR VIEW




This illustration is intended for interior reference only and may not represent the exterior of the model being specified.

DIMENSIONS



STANDARD INSTALLATION



NOTE: 3 1/2" (89) finished returns will be visible and should be finished to match cabin

