

SO30CM/B



## FEATURES

Preheats faster and cooks more consistently across all racks due to its advanced Dual VertiCross™ convection system

Assures predictably delicious results with a variety of modes, including Convection Roast, Proof, and Dehydrate

Prepares 50 popular dishes with the Gourmet feature that automatically adjusts cook times and temperatures

Handles multiple dishes simultaneously with our largest capacity oven (13 percent larger)

Insert a temperature probe to tell you exactly when it is done—and in gourmet mode, it will alert you the moment the dish is ready

Uncomplicate cooking with innovative, interactive color touchscreen controls

Blends in with a sleek black glass, handleless design

Integrates beautifully into surrounding cabinetry with flush installation

Ensures excellent visibility via three bright halogen lights and large, triple-panel-glass door windows

Master your technique with tips and recipes from the Mastering the M series oven guide

## ACCESSORIES

30" Broiler Pan

30" Premier Baking Sheet

Bake Stone Kit

Dehydration Kit

Dual Installation Kit

Full-Extension Ball Bearing Rack

Multi-Function Pan

Oven Rack

Oven Rack Set (3)

Temperature Probe

Accessories available through an authorized dealer.


For local dealer information, visit [subzero-wolf.com/locator](http://subzero-wolf.com/locator).



## PRODUCT SPECIFICATIONS


|                            |                                |
|----------------------------|--------------------------------|
| Model                      | SO30CM/B                       |
| Dimensions                 | 29 7/8"W x 28 1/2"H x 23"D     |
| Oven 1 Interior Dimensions | 25 1/4"W x 17 1/2"H x 19 7/8"D |
| Overall Capacity           | 5.1 cu. ft.                    |
| Usable Capacity            | 3.3 cu. ft.                    |
| Door Clearance             | 21 3/8"                        |
| Electrical Supply          | 240/208 VAC, 60 Hz             |
| Electrical Service         | 30 amp dedicated circuit       |
| Conduit Length             | 4 Feet                         |

## ELECTRICAL





**NOTE:** Dimensions in parenthesis are in millimeters unless otherwise specified


## DIMENSIONS



## FLUSH INSTALLATION



SIDE VIEW



FRONT VIEW

\*1" (25) minimum depth. Shaded areas will be visible and should be finished to match cabinetry.

\*\*Dimension provides minimum reveals

NOTE: Location of electrical supply within opening may require additional cabinet depth.