

MD24TE/S

FEATURES

Utilize 950 watts of power to cook meals with delicious results

Select from 10 power levels, a warming mode, and sensor cooking

Let the microwave do the cooking with intuitive "gourmet mode" settings

Fits a 9x13 pan and up to a 7" tall glass or dish for additional cooking flexibility

Install into surrounding cabinetry to coordinate with other Wolf built-in ovens and warming drawers

Installs can be lowered due to control panel lock providing extra safety

ACCESSORIES

Flush Inset Vent

Accessories available through an authorized dealer.


For local dealer information, visit subzero-wolf.com/locator.



PRODUCT SPECIFICATIONS


| | |
|--------------------|--------------------------------|
| Model | MD24TE/S |
| Dimensions | 23 7/8"W x 15 1/8"H x 21 7/8"D |
| Capacity | 1.2 cu. ft. |
| Electrical Supply | 120 VAC, 60 Hz |
| Electrical Service | 15 amp dedicated circuit |
| Power Cord Length | 4 Feet |
| Receptacle | 3-prong grounding-type |

ELECTRICAL





NOTE: Dimensions in parenthesis are in millimeters unless otherwise specified


DIMENSIONS



FLUSH INSTALLATION



SIDE VIEW



FRONT VIEW

*Will be visible and should be finished to match cabinetry.
**Dimension provides minimum reveals.