





# **One Kit Finds it All**

Water • Sewer • Gas • Electric • Telecomm CABLE TV LINES • CAST OR DUCTILE IRON PIPES **COPPER PIPE • CORNER MARKERS • CURB & VALVE BOXES ENCLOSURES • FIBER OPTIC W/ TRACER OR SHIELD** GAS LINES • HAZMAT DRUMS • IRRIGATION LINES **MAG & PK NAILS • MANHOLE COVERS • MARKER MAGNETS** PLASTIC PIPE W/TRACER WIRE • POWER LINES SEPTIC TANKS • STEEL PIPES • STREET LIGHT POWER TELEPHONE LINES • WATER & SEWER LINES • WELL CASINGS



















## **Rex Multi-Frequency Pipe & Cable Locator**







Slim, Sleek & Powerful Transmitter: 3.5 lbs and 1.75" thick

### **Rex Receiver** Specifications

Operating Frequency: Active: 512 Hz, 33 kHz and 82 kHz

Passive: 50 or 60 Hz Sonde: 512 Hz

Battery: One 9V Alkaline Battery
Battery Life: 12 Hours (intermittent usage)

Weight (incl. battery): 2.8 lbs (1.25 kg)

Operating Temperature: -4°F to 140°F (-20°C to 70°C)
Overall Dimensions: Closed: 17.5 in (~44 cm)
Extended: 27.7 in (~70 cm)

Max. Depth Capability: Approximately 19' (5.8 m)

Sonde mode - approximately 5' - 15'

(1.5 m to 4.2 m)

Water and Dust Resistance: Rated IP54

## **Rex Transmitter** Specifications

**Operating Frequency:** 512 Hz, 33 kHz and 82 kHz

Operating Modes: Conductive, Inductive, and Inductive Clamp

 Max. Output Power:
 512 Hz - 1/2, 1, 2 or 5 W

 (Conductive mode
 33 kHz - 1/2, 1, 2 or 5 W

 @ 1000 Ω load)
 82 kHz - 1/2 or 1

Battery Type: Rechargeable NiMH pack (12V)
Battery Life: 8 Hours (intermittent usage @ 70° F)
Charging: Internal Smart Charger powered by

AC/DC power adapter

Dimensions: 10"W x 10.25"D x 1.75" H (25.4 cm x 26 cm x 4.5 cm)

Weight: 3.5 lbs (1.6 kg)

Operating Temp.: -4°F to 140°F (-20°C to 70°C)

Backlighting: White LED array
Water and Dust Resistance: Rated IP54

# GA-92





### **GA-92XTd Receiver** Specifications

Battery Indicator: 4-segment LCD

Gain: 4-Level LCD - Low (L), Medium (M),

High (H), Extra High (XH)

Volume: 3 Levels, Muted, Medium and

Maximum

Input Power:

Battery Life:

One 9V Alkaline Battery

24 Hours (intermittent usage)

Operating Temperature:

-13° F to 140° F (-25° C to 60° C)

Overall Length:

Open – 26" (66 cm), Closed – 15.5"

(39 cm)

Nominal Sensor Spacing: 9.5" (24 cm)
Weight: 2.4 lbs (1.1 Kg)
Water and Dust Resistance: Rated IP54





