



ADJUSTABLE "J" HANGERS

Features

- Finish: Epoxy plated
- Color: Zinc
- MSS SP-58, Type 5



- A - Rod size (hanger rod and nuts not included)
- B - Center of pipe to top of hanger
- D - Rod take out (center of pipe to bottom of hanger rod)

Catalog Number	Pipe Size		Bolt Size	A	B		C		D		E		Design Load Lbs.	Weight Lbs.
	in.	mm.		(Rod Size)	in.	mm	in.	mm	in.	mm	in.	mm		
FNW7025EP0050	1/2	21.3	1/4-20UNC x 2-1/4	3/8-16UNC	2.32	58.85	0.96	24.50	1.35	34.35	0.41	10.30	400	0.18
FNW7025EP0075	3/4	26.7	1/4-20UNC x 2-1/4	3/8-16UNC	2.8	71.15	0.96	24.50	1.84	46.65	0.41	10.30	400	0.20
FNW7025EP0100	1	33.4	1/4-20UNC x 2-1/2	3/8-16UNC	2.91	73.8	1.08	27.50	1.82	46.30	0.41	10.30	400	0.22
FNW7025EP0125	1-1/4	42.2	1/4-20UNC x 2-3/4	3/8-16UNC	3.35	85.15	1.08	27.50	2.27	57.65	0.41	10.30	400	0.25
FNW7025EP0150	1-1/2	48.3	1/4-20UNC x 3	3/8-16UNC	3.43	87.1	1.32	33.50	2.11	53.60	0.41	10.30	400	0.25
FNW7025EP0200	2	60.3	1/4-20UNC x 3-1/2	3/8-16UNC	3.9	99.1	1.32	33.50	2.58	65.60	0.41	10.30	400	0.28
FNW7025EP0250	2-1/2	73.0	3/8-16UNC x 4-1/2	1/2-13UNC	4.55	115.5	2.07	52.50	2.48	63.00	0.56	14.30	800	0.58
FNW7025EP0300	3	88.9	3/8-16UNC x 5	1/2-13UNC	5.1	129.55	2.07	52.50	3.03	77.05	0.56	14.30	800	0.62
FNW7025EP0400	4	114.3	3/8-16UNC x 6-1/4	5/8-11UNC	6.11	155.1	2.13	54.00	3.98	101.10	0.56	14.30	800	0.91
FNW7025EP0500	5	141.3	3/8-16UNC x 8-1/2	5/8-11UNC	6.37	161.85	1.36	34.50	5.01	127.35	0.56	14.30	800	1.38
FNW7025EP0600	6	168.3	3/8-16UNC x 9-3/4	3/4-10UNC	7.7	195.6	1.81	46.00	5.89	149.60	0.56	14.30	1000	2.40
FNW7025EP0800	8	219.1	3/8-16UNC x 11	3/4-10UNC	9.4	238.65	2.20	56.00	7.31	185.65	0.56	14.30	1200	2.97