



ONE-LOK™ MODEL SLCE WEDGE RESTRAINT FOR PVC PIPE







PRODUCT SPECIFICATIONS

MATERIAL:

 Gland body, wedge inserts and break-off top actuating bolts are manufactured of high strength ductile iron in accordance with ASTM A536, Grade 65-45-12.

SIZE RANGE: •

DIMENSION:

Conform to ANSI/AWWA C111/A21.11 & ANSI/AWWA C153/A21.53 standards

PRESSURE RATING:

• Equal to the water working pressure rating of the pipe upon which it is installed with a minimum 2:1 factor of safety.

COATING:

Red Alkyd paint

3" - 60"

Electro-deposition "CORRSAFE™" available upon request. For further information, please refer to our CORRSAFE Product Information sheet at http://www.sigmaco.com/pipe-restraint-product-coatings-linings/

APPROVALS:

Underwriters Laboratories' listed in sizes 4"-12" to ASTM F1674 (latest revision) and Factory Mutual approved in sizes 4"-12".

DEFLECTION:

• 5° on 3"-12", 2° on 14"-16", 1.5° on 18"-30" and 1° on 36", 42", 48", 54" and 60"

TRACEABILITY:

• Gland body, wedge inserts and break-off top actuating bolts are individually cast with exact heat code information.

INSTALLATION:

• In accordance with manufacturer's recommendation and applicable AWWA standards.

