

6" Two Bolt Repair Clamps

Product Features

- Plated lug, carriage bolts and nuts for corrosion protection
- Stainless steel clamp with NBR gaskets for up to 180°F working temperature and pressure rating 150psi
 For use with Rigid Copper, PVC, Galvanixed, and Iron Pipe




Bands: 430 Stainless Steel Lugs: Class 30 Cast Iron

Gasket: NBR


Bolts & Nuts: Carbon Steel with Dichromatic zinc plated

*NBR resists oil-based hydraulic fluids, fats, animal and vegetable oils, flame retardant liquids, grease, water and air. Working temperature range -30° F to 180 ° F Pressure rating 150 psi



PFRCFU

Product Specifications



6" Two Bolt Clamp

	А		B (IPS/SCH.40)		B (CTS NOM.)	
MODEL NO.	in	mm	in	mm	in	mm
PFRCDU	6	152.4	1/2	12.7	3/4	10.05
PFRCFU	6	152.4	3/4	10.05	1	25.4
PFRCGU	6	152.4	1	25.4	1-1/4	31.75
PFRCHU	6	152.4	1-1/4	31.75	1-1/2	38.1
PFRCJU	6	152.4	1-1/2	38.1	-	-
PFRCKU	6	152.4	2	50.8	-	-

Warranty and Codes

This PROFLO product carries a 1-year limited warranty.